

Specifications



Eaton 8300W

Eaton Arrow Hart heavy-duty hospital grade duplex receptacle, #14-10 AWG, 20A, Healthcare, Flush, 125V, Back and side, White, Brass, High-impact nylon face, PVC base, 5-20R, Duplex, Screw, Nylon, PVC

General specifications

PRODUCT NAME	Eaton Arrow Hart heavy-duty hospital grade duplex receptacle
CATALOG NUMBER	8300W
UPC	032664705670
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	UL NOM Federal Specification Classification 6233 01
PRODUCT TYPE	Heavy-duty hospital grade



Powering Business Worldwide

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Auto-grounding
APPLICATION	Healthcare
DEVICE GRADE	Heavy-duty hospital grade
WIRING METHOD	Back and side
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
MATERIAL	Nylon, PVC
COLOR	White
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	#14-10 AWG
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	PVC base High-impact nylon face
RECEPTACLE TYPE	Duplex

Resources

MULTIMEDIA	Residential straight blade receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 8300W Arrow Hart heavy-duty hospital grade straight blade duplex receptacles

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton 8300W

Eaton Arrow Hart heavy-duty hospital grade duplex receptacle, #14-10 AWG, 20A, Healthcare, Flush, 125V, Back and side, White, Brass, High-impact nylon face, PVC base, 5-20R, Duplex, Screw, Nylon, PVC

General specifications

PRODUCT NAME	Eaton Arrow Hart heavy-duty hospital grade duplex receptacle
CATALOG NUMBER	8300W
UPC	032664705670
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	UL NOM Federal Specification Classification 6233 01
PRODUCT TYPE	Heavy-duty hospital grade



Powering Business Worldwide

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Auto-grounding
APPLICATION	Healthcare
DEVICE GRADE	Heavy-duty hospital grade
WIRING METHOD	Back and side
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
MATERIAL	Nylon, PVC
COLOR	White
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	#14-10 AWG
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	PVC base High-impact nylon face
RECEPTACLE TYPE	Duplex

Resources

MULTIMEDIA	Residential straight blade receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 8300W Arrow Hart heavy-duty hospital grade straight blade duplex receptacles

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

