



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 89045 Omniconn RG-6 Quad F CMPRSN Conn Black, 50/Jar

*Ideal*

Catalog Number	89045
Manufacturer	Ideal
Description	Ideal, Compression Connector, Omniconn, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 Ohm, Ports Size: 7/16 In, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 In, Overall Jacket Diameter: 0.260 - 0.280 In
Weight per unit	0.9500 (lbs/each)
Product Category	Coaxial & Twinaxial Connectors

### Features

Material	Brass
----------	-------

### Material, Color, and Finish

Finish	Nickel
--------	--------

### Descriptions

Description	OMNICONN RG-6 QUAD F CMPRSN CONN BLACK, 50/JAR
Features	Connector Model: 6QFOAccepts RG-6 Quad coax cablesCenter conductor range: AllDielectric diameter range: .175 - .183 Outer jacket diameter range: .270 - .295 Recommended cable prep/stripping tools: 45-605 PrepPRO ; 45-526Recommended compression tools: 30-793 OmniSeal PRO XL; 33-632 Linear X®3The IDEAL OmniConn F connector is a cable specific connector solution for RG-6 coax. The OmniConn connectors have a combination brass and plastic exterior and an inner O-ring to provide a weather proof connection s
Long Description	IDEAL, Compression Connector, OmniCONN, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 OHM, Ports Size: 7/16 IN, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 IN, Overall Jacket Diameter: 0.260 - 0.280 IN
Product Type	RG6 Quad Compr Conn, Omni, 50JR
Special Features	Features: OmniCONN F compression connectors install easily onto standard RG 6 and RG 6Quad cables; Non corrosive nickel plated brass body and polycarbonate bushing; Delrin/Nylon adapter sleeve and o-ring provide double protection for a watertight seal; Free spinning hex nut for ease of installation onto all 7/16 IN ports 75 OHM nominal impedance; Bandwidth up to 3 GHZ; Nominal Impedance: 75 OHM; Ports Size: 7/16 IN; Coaxial Cable Type: RG-6; Bandwidth: 3 GHZ; Dielectric Diameter: 0.175 - 0.183 IN; Overall



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Ideal
GTIN	00783250890453
Manufacturers Part Number	89-045
sub brand	OmniCONN
UPC	783250890453

## Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	F-Type

## Availability

minimum qty	50
-------------	----

## Packaging

Carton	50
Weight Per each	0.95

## Uses, Certifications, and Standards

Application	Terminating an F Style connection onto RG 6 Quad Coax .
-------------	---