

Exhaust Fan with Light Housing

Fan Housing

23 gauge galvanized metal housing. Dimensions 7^3 /s" x 7^5 /s" x 5^7 /s".

Duct Collar

Plastic collar for 4" duct connection, comes complete with built in non-metallic back draft damper for quiet operation.

Unit Mounting

Rated Type IC for ceilings insulated to R-40. Designed to mount in ceilings with at least 6" of clearance. The unit will mount directly to the joist or using the supplied mounting bars with a rough in opening of 75%" x 77%". The housing will mount through drywall thickness up to 34".

• Electrical Connections


1/2" electrical knockouts provided.

Available Trim Kits


ASLC50MBG: 50 CFM **ASLC70MBG**: 70 CFM

Shipping Info

Number of Housings in Box: 4 UPC Code: 083162225115



Housing ONLY. Must be combined with ASLCMBG series trim kit (sold separately)





820 Lincoln Avenue West Chester, Pennsylvania 19380-4466 Tel: (610) 692-7400 ● 877-304-3785 Fax: (610) 696-8048

Specifications subject to change without notice. Updated 10-15