



89610 Barrier Strip, 12-Circuit

Ideal

Catalog Number	89610
Manufacturer	Ideal
Description	Barrier Strip, 12 Circuits, 10 Poles, 30 A, 300/400 V, Plastic, +221 °F, 4.626 In Overall Length, 0.795 In Overall Width, 0.570 In Overall Height, 0.13 LB
Weight per unit	0.1330 (lbs/each)
Product Category	Power BLKS & Distribution BLKS

Features

amperage rating	30, 20
Material	Plastic Housing
Voltage Rating	300, 400
Wire Size	22-10, 22-18

Descriptions

Description	BARRIER STRIP, 12-CIRCUIT
extra long description	IDEAL 89-610 TERMINAL BLOCK 12 POL
Features	IDEAL Barrier Strips are designed and manufactured to be rugged, reliable, and easy to use. A thermoplastic base and corrosion-resistant screws and hardware provide extended service life.
Special Features	Features: UL Recognized For 30A, 300V; CSA Certified For 20A, 400V; Torque Rating Of 4.4 In-Lbs; Recessed Screws And Tubular Contacts; UL Listed And CSA Certified; Connect Stripped Un-Terminated Solid Or Stranded Wire; Modular 12 Circuits Can Be Cut Into Smaller Sections; Plastic Housing Is UL Flame Rated To 94V-2; Rated Temperature To 105 Degrees C; Recessed Screws And Tubular Contacts Provide Added Safety And Help Prevent Short Circuits; Tubular Contacts Connect Stripped, Un-Terminated Solid Or Stranded W

Manufacturer Information

Brand	Ideal
GTIN	00783250896103
UPC	783250896103

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

Packaging

Carton	1
Weight Per each	0.133

Uses, Certifications, and Standards

standard	C/US UL Listed, RoHS
----------	----------------------