



Part Number: 9329
300V PLTC, (3 pr) 22 AWG (7x30) TC, PVC/PVC, Individual Shld, CMG

 [Request Sample](#)

Product Description
Three 22 AWG pairs stranded (7x30) tinned copper conductors, PVC insulation, individual Beldfoil® shield (100% coverage), PVC jacket .

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	3

Conductor Count:	6
Total Number of Pairs:	3
Total Number of Triads:	N/A
Conductor Size:	22 AWG

Insulation	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.062 in

Color Chart	
Number	Color
1	Black & Red and Numbered 1
2	Black & Red and Numbered 2
3	Black & Red and Numbered 3

Inner Shield Material						
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	22	7x30 mm

Outer Shield Material	
Material	Unshielded

Outer Jacket Material				
Material	Nominal Diameter	Nominal Wall Thickness	Ripcord	
PVC - Polyvinyl Chloride	0.341 in	0.042 in	Yes	

Construction and Dimensions

Cabling	
Lay Direction	Left-hand Lay

Print Legend:	LEGEND: BELDEN 9329 E34972 3PR22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
---------------	--

Electrical Characteristics

Conductor DCR	
Individual Pair Nominal Shield DCR	Nominal Conductor DCR
76 Ohm/1000ft	15 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
26 pF/ft	45 pF/ft

Inductance

Nominal Inductance
0.21 µH/ft

Current

Max. Recommended Current [A]
3.4 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V RMS
150 V RMS (ITC)

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	60 lbs/1000ft
Max Recommended Pulling Tension:	54 lbs
Min Bend Radius/Minor Axis:	3.5 in

Standards

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
CSA AWM Specification:	2464

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1685 FT4 Loading
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
9329 0601000	Chrome	C
9329 060500	Chrome	C
9329 0605000	Chrome	Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2018 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.



Part Number: 9329
300V PLTC, (3 pr) 22 AWG (7x30) TC, PVC/PVC, Individual Shld, CMG

 [Request Sample](#)

Product Description
Three 22 AWG pairs stranded (7x30) tinned copper conductors, PVC insulation, individual Beldfoil® shield (100% coverage), PVC jacket .

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	3

Conductor Count:	6
Total Number of Pairs:	3
Total Number of Triads:	N/A
Conductor Size:	22 AWG

Insulation	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.062 in

Color Chart	
Number	Color
1	Black & Red and Numbered 1
2	Black & Red and Numbered 2
3	Black & Red and Numbered 3

Inner Shield Material						
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	22	7x30 mm

Outer Shield Material	
Material	Unshielded

Outer Jacket Material				
Material	Nominal Diameter	Nominal Wall Thickness	Ripcord	
PVC - Polyvinyl Chloride	0.341 in	0.042 in	Yes	

Construction and Dimensions

Cabling	
Lay Direction	Left-hand Lay

Print Legend:	LEGEND: BELDEN 9329 E34972 3PR22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
---------------	--

Electrical Characteristics

Conductor DCR	
Individual Pair Nominal Shield DCR	Nominal Conductor DCR
76 Ohm/1000ft	15 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
26 pF/ft	45 pF/ft

Inductance

Nominal Inductance
0.21 µH/ft

Current

Max. Recommended Current [A]
3.4 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V RMS
150 V RMS (ITC)

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	60 lbs/1000ft
Max Recommended Pulling Tension:	54 lbs
Min Bend Radius/Minor Axis:	3.5 in

Standards

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
CSA AWM Specification:	2464

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1685 FT4 Loading
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
9329 0601000	Chrome	C
9329 060500	Chrome	C
9329 0605000	Chrome	Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2018 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.