



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AYP040 4/0 Al/Cu Offset Comp Terminal

Burndy LLC

Catalog Number	AYP040
Manufacturer	Burndy LLC
Description	Aluminum Compression Pin Adapter, 4/0 Awg, 0.42" Plug Dia, 1.22" Plug Length, Al/Cu Rated, Tin Plated.
Weight per unit	0.1200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Type	CODE/FLEX
Die Index	298
insulation	Y
Insulation Type	Rubber
Material	Aluminum
pallet quantity	2960
Voltage Rating	35,000

Material, Color, and Finish

Color Code	WHITE
Finish	Tin-Plated

Descriptions

Description	4/0 AL/CU OFFSET COMP TERMINAL
extra long description	BUR AYPO4/0 4/0STR AL OFFSET HYPLUG
Long Description	Aluminum Compression Pin Adapter, 4/0 AWG, 0.42" Plug Dia, 1.22" Plug Length, Al/Cu Rated, Tin Plated.
Product Type	Terminal
Special Features	Features: All-Aluminum Electro-Tin Plated Design: Eliminates Possible Bi-Metallic Corrosion And Provides The Shortest Connector Length Design Possible, Shortest Connector Length Design Possible: Permits Easy Installation In Equipment With Limited Working Space, Solid Electro-Tin Plated Aluminum Plug: Proper Electrical Connection Made Easily, Eliminates How Tight Is Tight Problem, Smooth Surface On The Solid EC Aluminum Electro-Tin Plated Plug: Provides Greater Area Contact Establishing Excellent Electrical

Manufacturer Information

Brand	BURNDY
GTIN	00781810738368
Manufacturers Part Number	AYPO4/0
sub brand	HYPLUG
UPC	781810738368



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Aluminum Pin Adapters

Packaging

Carton	1
Package	10
Weight Per each	0.12

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B
Temperature Rating	194