



Part Number: 9329

300V PLTC, (3 pr) 22 AWG (7x30) TC, PVC/PVC, Individual Shld, CMG

Request Sample

Product Description

Three 22 AWG pairs stranded (7x30) tinned copper conductors, PVC insulation, individual Beldfoil® shield (100% coverage), PVC jacket .

Technical Specifications

Physical Characteristics (Overall)

Conductor AWG Stranding Material No. of Pairs 22 7x30 TC - Tinned Copper 3 Conductor Count: 6 Total Number of Pairs: 3 Total Number of Triads: N/A Conductor Size: 22 AWG

Insulation

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.062 in

Color Chart

Number	Color
1	Black & Red and Numbered 1
2	Black & Red and Numbered 2
3	Black & Red and Numbered 3

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	22	7x30 mm

Outer Shield Material



Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.341 in	0.042 in	Yes

Construction and Dimensions

Cabling

Lay Direction
Left-hand Lay

Print Legend:

LEGEND: BELDEN 9329 E34972 3PR22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
76 Ohm/1000ft	15 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
26 pF/ft	45 pF/ft

Inductance

Nominal Inductance 0.21 µH/ft

Current

Max. Recommended Current [A] 3.4 Amps per conductor @ 25°C

Voltage

300 V RMS 150 V RMS (ITC)

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	60 lbs/1000ft
Max Recommended Pulling Tension:	54 lbs
Min Bend Radius/Minor Axis:	3.5 in

Standards

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
CSA AWM Specification:	2464

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1685 FT4 Loading
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
, ,	

Part Number

Variants

Item #	Color	Footnote
9329 0601000	Chrome	С
9329 060500	Chrome	С
9329 0605000	Chrome	Z
3329 0605000	Chrome	

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2018 Belden, Inc

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.