



PRODUCT DATA SHEET

Controlled Document - Engineering Drive


1530 Shields Drive
Waukegan, IL 60085
Toll-Free (800) 323-9355
Fax: (847) 689-1192

PART NUMBER: 95218
DESCRIPTION: 18/3 STRANDED SHIELDED CMR/CL3R/FPLR FT4 CABLE
CONSTRUCTION: This cable consists of three bare copper insulated conductors with an overall shield with a drain. The overall assembly has an overall jacket.
APPROVALS: UL Standard 13 and 444, NEC Articles 725 and 800.
APPLICATION: Class 3 Power Limited Circuit Cable and Communications Cable for Riser Applications

Construction Parameters:

Cable Cross-Section

Conductor 18 AWG Bare Copper
Stranding 7/.0152"
Insulation Material PVC
Insulation Thickness 0.008" Nom.
Insulated Conductor Diameter 0.062" Nom.
Number of Conductors 3
Lay Length 4.00" Nom.
Shield Alum/Mylar
Drain 24 AWG Stranded Tinned Copper
Jacket Material PVC
Jacket Thickness 0.014" Nom.
Overall Cable Diameter 0.171" Nom.
Approximate Cable Weight 26.5 Lbs/1M' Nom.
Flame Rating UL 1666 Riser Flame Test



Electrical & Environmental Properties:

Temperature Rating -20°C to 60°C
Operating Voltage 300 V RMS Max.
Capacitance Between Conductors @ 1 KHz 59 pF/ft Nom.
Capacitance Between Conductors to Shield @ 1 KHz 109 pF/ft Nom.
DC Resistance per Conductor @ 20°C 6.29 Ohms/1M' Nom.

Insulation Colors Black Red White
Jacket Color Gray (Other colors available for minimum order)

Legend (Surface Ink Print) COLEMAN CABLE 95218 18 AWG 3/C C(ETL)US (ETL CODE) TYPE CMR/CL3R/FPLR
SUN RES -- CMX OUTDOOR-- TYPE CMG FT4

This product complies with European Directive 2002/95/EC (RoHS)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

Cable has a rip cord for easy jacket removal. The jacket is sequentially footmarked.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control, all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name _____

Customer Approval _____

Specification Issue Date: June 18, 2007

Packaging Options

Coleman Cable offers four types of packaging options.

- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

* Not all options are available for each product



Coleman Cable Part Legend



Put-ups	Code	Colors	Code		Code
Reel, 250 ft	04	White	01	Pink	11
Reel, 500 ft	05	Yellow	02	Purple	13
Reel, 1,000 ft	06	Orange	03	Clear	18
Reel-in-box, 1,000 ft	16	Red	04	Fluorescent	
RabbitPull™ Pull-Box, 500 ft	45	Green	05	Pink	21
RabbitPull™ Pull-Box, 1,000 ft	46	Blue	06	Ivory	22
SignaCoil™ 500 ft	55	Brown	07	Natural	23
SignaCoil™ 1,000 ft	56	Black	08	Beige	33
		Gray	09	Red Striped	
				CorraClad™	44

