


SPECIAL PURPOSE PLIERS




PLIER	A OVERALL LENGTH		B JAW LENGTH		C JOINT THICKNESS		D JOINT WIDTH		E CUTTING EDGE		H HANDLE SPAN		WEIGHT	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	pounds	grams
908	8.25	209.55	1.68	42.67	0.34	8.64	1.48	37.59	0.49	12.45	2.18	55.37	0.48	217.72

Features

- Strips wire with no damage to conductor.
- Crimps insulated and non-insulated wire.
- Dénude le fil sans endommager le conducteur.
- Serit les fils isolés et non-isolés.
- Desforra alambres sin daño alguno al conductor.
- Poncha alambres aisladas y no aisladas.

Features

- Retaining ring pliers
- Converts from internal to external rings with simple switch of the red tab.
- 929 – External: 1½" to 4", Internal: 113/16" to 4" Includes tips: .090, .108, .120 15° and .090, .108, .120 90°
- 927 – External: 1/4" to 2", Internal: 3/8" to 2" Includes tips: .036, .047, .070 straight and .036, .047 90°
- 926 – External: 1/8" to 1", Internal: 1/4" to 1" Includes tips: .023, .036, .047 straight and .036, .047 90°
- Pince pour anneau élastique
- Convertissable de circlips intérieur à circlips extérieur en déplaçant simplement le bouton rouge.
- 929 – Circlips extérieurs : 38.1 à 101.6 mm, intérieurs : 46.04 à 101.6 mm. Comprend les embouts suivants : 2.29, 2.74, 3.05 mm coudés à 15° et 2.29, 2.74, 3.05 mm coudés à 90°
- 927 – Circlips extérieurs : 6.35 à 50.80 mm, intérieurs : 9.53 à 50.80 mm. Comprend les embouts suivants : 0.91, 1.19, 1.78 mm droits et 0.91, 1.19 mm coudés à 90°
- 926 – Circlips extérieurs : 3.18 à 25.40 mm, intérieurs : 6.35 à 25.40 mm. Comprend les embouts suivants : 0.58, 0.91, 1.19 mm droits et 0.91, 1.19 mm coudés à 90°
- Pinza para anillo de retención
- Convierte para usarse en anillos internos o externos con un simple cambio de la lengüeta roja.
- 929: Externos: 38.1 a 101.6 mm; Internos: 46.04 a 101.6 mm. Incluye puntas de 2.29, 2.74 y 3.05 mm de 15° y 2.29, 2.74 y 3.05 mm de 90°.
- 927: Externos: 6.35 a 50.80 mm; Internos: 9.53 a 50.80 mm. Incluye puntas de 0.91, 1.19 y 1.78 mm rectas y 0.91 y 1.19 mm de 90°.
- 926: Externos: 3.18 a 25.40 mm; Internos: 6.35 a 25.40 mm. Incluye puntas de 0.58, 0.91 y 1.19 mm rectas y 0.91 y 1.19 mm de 90°.




PLIER	A OVERALL LENGTH		B JAW LENGTH		C JOINT THICKNESS		D JOINT WIDTH		E CUTTING EDGE		H HANDLE SPAN		WEIGHT	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	pounds	grams
929	10.00	254.00	1.38	35.05	1.00	25.40	1.25	31.75	N/A	N/A	4.75	120.65	1.06	480.81
927	8.00	203.20	1.60	40.64	0.97	24.64	1.71	43.43	N/A	N/A	4.85	123.19	0.50	226.80
926	6.25	158.75	1.31	33.27	0.87	22.10	1.12	28.45	N/A	N/A	3.29	83.57	0.32	145.15

U.S. Patent No. 7,194,936 B2

Features

- Locknut plier
- Fits most popular UL locknut sizes. (metal, PVC, plastic)
- Thin profile for confined spaces.
- Pincas à contre-écrou
- Convient aux tailles d'écrou d'arrêt les plus communes (métal, PVC, plastique).
- Profil effilé pour espaces confinés.
- Alicata para contratruercas
- Se ajusta a los tamaños más populares de contratruercas (metal, PVC, plástico).
- Perfil delgado para espacios estrechos.



PLIER	A OVERALL LENGTH		B JAW LENGTH		C JOINT THICKNESS		D JOINT WIDTH		E CUTTING EDGE		H HANDLE SPAN		WEIGHT	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	pounds	grams
960	8.50	215.90	2.38	60.45	0.21	5.33	0.92	23.37	N/A	N/A	2.54	64.52	0.48	217.72

U.S. Patent No. 7,197,967