



## Occupancy & Vacancy Sensors & Timers make saving energy and saving money easy.

- Occupancy sensors turn lights on when you enter a room and save energy by automatically turning them off when room is unoccupied.
- Vacancy sensors save more energy by requiring anyone entering the room to manually turn on the lights. When the room is unoccupied, the lights will turn off.
- Using occupancy and vacancy sensors may contribute to LEED certification and help make buildings sustainable.

*P&S Sensors and Timers help meet energy codes. They are convenient, easy-to-install, and compatible with all standard types of lighting.*

*Sensors add to the comfort, safety and security of the people who occupy the building.*

*Timers turn loads off when no longer needed.*



## Index

Device	Page Number
Technology	L-2
Applications	L-3
Residential Vacancy Sensors	L-4
Residential Occupancy Sensors	L-5
Residential Occupancy/Vacancy Sensors	L-6, L-7
Commercial Occupancy Sensors	
PlugTail™ Wall Box	L-8
Wall Box	L-8
Dual Technology Wall Box	L-9
Wall or Ceiling Mount	L-12
Ceiling Mount	L-13
Ultrasonic Ceiling Mount	L-14
Dual Technology Ceiling Mount	L-15
Commercial Occupancy/Vacancy Wall Box Sensors	L-10, L-11
Power Packs & Add-A-Relay	L-16
Useful Calculations	L-17
Timers	L-18, L-19
Wall Box Timers	L-20

## Occupancy & Vacancy Sensors & Timers Technology



### Passive Infrared Sensors (PIR)

Using a patented fresnel lens which minimizes optical aberrations, each Legrand/Pass & Seymour PIR sensor breaks its coverage area into zones. Upon detecting an infrared energy change within a zone, one of the elements in the dual-element pyroelectric sensing device of an occupancy sensor generates a positive pulse. Within milliseconds, the other element produces a negative pulse and the lights are turned on. Vacancy sensors turn lights off when the room is vacant for a period of time, or when there is no infrared energy detected within a zone.

Passive infrared sensors are unable to detect occupancy around barriers, and are more effective when sensing movement across their field of sight rather than towards or away from it.

#### All Legrand/Pass & Seymour PIR occupancy sensors feature:

- Patented fresnel lenses with multi-segment design
- Dual-element pyroelectric sensors
- Low-profile design
- Daylight filter systems
- Adjustable settings for time and sensitivity
- Custom Detection Signature Analysis for high immunity to RFI and EMI, and reliability
- Self-adaptive technology is available on some models

### Ultrasonic Sensors

Ultrasonic sensors use a multi-directional transmitter/receiver system to broadcast ultrasonic sound waves generated by a quartz crystal oscillator, and then measure the amount of time it takes the waves to return. Movement within the area results in the sound waves returning to the sensor at a slower or faster rate, and thus occupancy is detected.

Ultrasonic sensors broadcast in three dimensions, and are therefore able to detect smaller movements than PIR sensors. Proper placement of the sensors is essential as sound waves can escape through open doorways, resulting in false triggering.

While Legrand/Pass & Seymour ultrasonic sensors use special circuitry to filter out air-flow movement caused by HVAC equipment or fans, sensors should be kept away from breezy areas. Also, heavy carpeting and other sound-absorbing materials used in the construction of a room will reduce coverage.

#### Legrand/Pass & Seymour ultrasonic occupancy sensor features:

- Temperature- and humidity-resistant tuned receivers
- Signal Processing Circuitry
- Solid-state, crystal-controlled transmitter
- Adjustable controls for time and sensitivity

### Dual Technology

Dual Technology sensors combine PIR and Ultrasonic sensing in one device. This minimizes false ONs and nuisance OFFs. Sensitivity adjustments and user selectable operational characteristics make dual technology sensors the most versatile, even in the most difficult installations.

Use dual technology sensors for the most demanding sensor applications. Odd shaped rooms, lots of partitions, and changing floor plans can be handled best by dual technology sensors.



# Occupancy & Vacancy Sensors & Timers Applications



Pass & Seymour


P&S Model	Catalog Page #	Best Suited For:
<b>Residential Occupancy Sensors</b>		
RW500U	L-5	Storage rooms, walk-in closets, pantries, garage where no neutral is available
RWU600U	L-5	Storage rooms, walk-in closets, pantries, garage where a neutral is available
<b>Residential Vacancy Sensors (T24 Compliant)</b>		
RW500B	L-4	Bedrooms, basements bathrooms, laundry rooms, where no neutral is available
RWU600B	L-4	Bedrooms, basements bathrooms, laundry rooms, where a neutral is available
RW600BTC	L-4	Bedrooms, basements bathrooms, laundry rooms, where no neutral is available
<b>3-Way Residential Occupancy/Vacancy Sensor</b>		
RW3U600	L-6	Any room/hall with multiple entrances — allows manual ON/OFF control from both locations. Can be switched between occupancy and vacancy.
RW3U603	L-6	<b>T24 Compliant.</b> Any room/hall with multiple entrances — allows manual ON/OFF control from both locations. Can be switched between occupancy and vacancy.
<b>Residential Occupancy/Vacancy Sensor with Dimmer</b>		
RWDU500	L-7	Any room where adjustable light level is desired
<b>Commercial Passive Infrared (PIR) Wall Box Sensors</b>		
PTWSP250	L-8	Small offices, closets, utility rooms with no partitions or obstructions
WSP250	L-8	Small offices, closets, utility rooms with no partitions or obstructions
OS300S	L10	Small offices, closets, small conference rooms with no partitions or obstructions
OSR300S	L-11	Small rooms with two individually-controlled loads or bi-level lighting with no partitions or obstructions
<b>Commercial Passive Infrared (PIR) and Ultrasonic Wall Sensors</b>		
WDT100	L-9	Small offices, executive suites, conference rooms, break rooms.
WDT200	L-9	
<b>Commercial Passive Infrared (PIR) Ceiling Sensors</b>		
CS500	L-13	Open offices, lunch, utility, storage, and computer rooms with no partitions or obstructions
CS1200	L-13	Larger rooms, up to 1200 sq. ft., with open floor plans, no partitions or obstructions
<b>Commercial Passive Infrared (PIR) Wall or Ceiling Mount Sensors</b>		
HS1001	L-12	Hallways, or aisles
WA1001	L-12	Entrances, vestibules, classrooms, for wide-angle applications
<b>Commercial Ultrasonic Ceiling Mount Sensors</b>		
CSU600	L-14	Offices, computer, meeting, copy, and restrooms
CSU1100	L-14	Offices, lunch, break and classrooms, restrooms, and conference rooms
CSU2200	L-14	Offices, lunch, break and classrooms, restrooms, conference rooms, halls, storage areas
<b>Commercial Dual Technology Sensors</b>		
CSD1000	L-15	Meeting, conference and classrooms, restrooms, dressing rooms, libraries, interview rooms, testing areas, lunch and break rooms
<b>Timers</b>		
RT1	L-18	Closets, bathroom fans, exhaust fans, heat lamps, bedrooms
RT12	L-19	Garages, basements, laundry rooms, fans, motors, landscape lights
RT24	L-19	Exterior lights, landscape lighting, security lighting, holiday lighting
97015, 30, 60	L-20	Bathroom fans, heat lamps, guest rooms
97115, 30, 60	L-20	Bathroom fans, heat lamps, guest rooms where a hold function is desired
97352	L-20	Dual control for bathroom light and fan



Pass &amp; Seymour

## Occupancy & Vacancy Sensors & Timers Wall Box Timers


125, 125-T, 250 &amp; 277VAC, 60 Hz



97015I

Catalog Number	Color
<b>Replacement Knobs (without plate)</b>	
PS55A1	White
PS55B1	Ivory
PS55G1	Light Almond

VAC	Hz	Amp	HP
<b>Ratings</b>			
125	60	20	1
125T	60		7
250	60	10	1
277	60	10	



97352I

### Applications

- Lighting
- Whirlpools and spas
- Heating and heat lamps
- Exhaust fans
- Saunas
- Ventilating and air conditioning

### Features

- Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.
- Turning clockwise causes unit to time load off after desired time delay.
- Quiet operation.
- Time range from 5 minutes to 12 hours.
- Available with or without hold.
- Decorator styling.
- Easily installed.
- Large head screw terminals.
- Accurate to  $\pm 5$  percent.
- Motor rated.
- Energy saving.

Catalog Number	Description	Time Range	Color
<b>Specification Grade Decorator Rotary Timers</b>			
97015I 97015W 97015LA	Timeout, No Hold	15 Minutes	Ivory White Light Almond
97030I 97030W 97030LA	Timeout, No Hold	30 Minutes	Ivory White Light Almond
97060I 97060W	Timeout, No Hold	60 Minutes	Ivory White
97115I 97115W	Timeout, With Hold	15 Minutes	Ivory White
97160I 97160W	Timeout, With Hold	60 Minutes	Ivory White

### Features


- Eliminates the need for two switches.
- Fits standard toggle opening for easy ganging.
- Time range adjustable from 1-60 minutes.
- Easily installed.
- May control one or two loads simultaneously.
- Motor rated.
- Silent operation.
- Reliable solid-state construction.
- Energy saving.

Catalog Number	Description	Time Range	Rating	Color
<b>Specification Grade Toggle Time Delay Switches Center Off</b>				
97352I 97352W	Double Pole, Double Throw	1-60 Minutes, Adjustable	500W, 1/3 HP, 120VAC, 60 Hz	Ivory White

### Operation: Catalog Number 97352

- When toggle is up, one or two loads remain on.
- When toggle is down, load "A" is off, load "B" times-off at preset time. In the center position, both loads are off.

### Wiring Diagram: Single Timed Load Application



All devices listed on this page conform to NEMA WD-1 and WD-6.