



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BMSE1501 Carbon STL Serv Ent Staple, 1-5/16"X3/4", 100/Box

Ideal

| | |
|------------------|--|
| Catalog Number | BMSE1501 |
| Manufacturer | Ideal |
| Description | Ideal, Cable Staple, Staple Size: 1-5/16 X 3/4 In, Cable Type: Seu, Material: Carbon Steel |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Nails, Staples, Rivets |

Features

| | |
|------------|--------------|
| Cable Type | SEU |
| Material | Carbon Steel |

Descriptions

| | |
|------------------------|--|
| Description | CARBON STL SERV ENT STAPLE, 1-5/16"X3/4", 100/BOX |
| extra long description | IDEAL BMSE150-1 STAPLE 100PC, SEU 1 |
| Features | Use with service entrance cable and conduitHigh-grade carbon steel constructionSharp-point legs drive straight without splitting woodResist rust and corrosion |
| Long Description | IDEAL, Cable Staple, Staple Size: 1-5/16 X 3/4 IN, Cable Type: SEU, Material: Carbon Steel |
| Product Type | Staple 100PC, Seu 1 5 16 X 3 4 |
| Special Features | Features: Use With Service Entrance Cable And Conduit; High-Grade Carbon Steel Construction; Sharp Point Legs Drive Straight Without Splitting Wood; Resist Rust And Corrosion |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00781789455686 |
| Manufacturers Part Number | BMSE150-1 |
| UPC | 781789455686 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
|----------------------|--|

Availability

| | |
|-------------|------|
| minimum qty | 5000 |
|-------------|------|

Packaging

| | |
|-----------------|------|
| Carton | 5000 |
| Weight Per each | 1.22 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Service Entrance Cable And Conduit |
| standard | RoHS |