



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AB204EG 3 Hole 90 Degree "L" Electro Galvanized Fitting

*Thomas&Betts-Abb Ins Prod*

Catalog Number	AB204EG
Manufacturer	Thomas&Betts-Abb Ins Prod
Description	90 Degree Fitting, Steel, Silver Galvanized, Silver, 3-1/2 In Length, 2-1/4 In Height, 1/4 In Thickness, 9/16 In Hole Size, 3 Holes, 54.5 LB/100
Weight per unit	0.5500 (lbs/each)
Product Category	Channel & Strut Fittings

### Material, Color, and Finish

material composition	Steel IN
----------------------	----------

### Descriptions

Description	3 HOLE 90 DEGREE "L" ELECTRO GALVANIZED FITTING
-------------	---

### Manufacturer Information

Brand	Superstrut
GTIN	00616013007495
UPC	616013007495

### Taxonomies, Classifications, and Categories

Category Description	MISC FITTINGS
Type	90 degree Angle Fittings

### Packaging

Carton	1
Package	50
Weight Per each	0.55

## Fittings and Brackets

### Fittings and Brackets — Series 200



#### Material

Superstrut® fittings and brackets are manufactured from hot rolled carbon steel.

#### Dimensions

The following standard dimensions apply to all fittings except as indicated on the individual drawings.

- Hole spacing:  $1\frac{3}{16}$ " from end of fittings
- Hole spacing:  $1\frac{1}{8}$ " centers
- Hole size:  $\frac{9}{16}$ " diameter
- Material:  $1\frac{1}{2}$ " wide
- Material:  $\frac{1}{4}$ " thickness

#### Application Instructions

Parts drawings illustrate a typical use for the fitting, and in many cases other uses for the part are appropriate.

#### Design Data

Ratings vary when used with 12 or 14 gauge channel and are shown for each channel material.


GoldGalv® hardware finish is standard for all Superstrut® products. This is a multi-process finish of electro-plated zinc, followed by gold-colored trivalent chromium to give excellent corrosion resistance and a superior paint base. See pages B-106–B-107 for complete description of the GoldGalv® hardware finish. GoldGalv® hardware will be furnished if no other finish is specified.

#### Nuts and Bolts Required


Unless otherwise noted, nuts and bolts for use with fittings and brackets should be ordered separately.

The standard bolt for the  $\frac{9}{16}$ " hole is a  $\frac{1}{2}$ " hex head cap screw  $1\frac{5}{16}$ " long. The  $1\frac{1}{16}$ " length may be used with all series channel.


Standard Finish — GoldGalv®, unless otherwise stated.




CAT. NO. AB201




CAT. NO. AB202




CAT. NO. AB203




CAT. NO. AB204




CAT. NO. AB205




CAT. NO. AB206




CAT. NO. AB207




CAT. NO. AB213




CAT. NO. AB214




CAT. NO. AB216



CAT. NO. AB219



CAT. NO. AB220



CAT. NO. AB240

#### Standard Dimensions

- Hole Spacing:  $1\frac{3}{16}$ " From End
- Hole Spacing:  $1\frac{1}{8}$ " Centers
- Hole Size:  $\frac{9}{16}$ " Diameter
- Material:  $1\frac{1}{2}$ " Width
- Material:  $\frac{1}{4}$ " Thick

Standard Finish — GoldGalv®, unless otherwise stated.  
Add EG suffix for SilverGalv® Finish