

Straight Blade Receptacles Commercial Specification Grade Receptacles


15 & 20A, 125V

Pass & Seymour



Features

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- CR Series: #14 – #10 AWG solid side wire only. BR Series: side and internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.



CR15I

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 C22.2 No. 42
Duplex Receptacles Side Wire					
CR15I	15 125	Ivory	5-15R	•	•
CR15W	15 125	White	5-15R	•	•
CR15	15 125	Brown	5-15R	•	•
CR15GRY	15 125	Gray	5-15R	•	•
CR15LA	15 125	Light Almond	5-15R	•	•
CR20I	20 125	Ivory	5-20R	•	•
CR20W	20 125	White	5-20R	•	•
CR20	20 125	Brown	5-20R	•	•
CR20GRY	20 125	Gray	5-20R	•	•
CR20BK	20 125	Black	5-20R	•	•
CR20RED	20 125	Red	5-20R	•	•
CR20LA	20 125	Light Almond	5-20R	•	•
Duplex Receptacles Back & Side Wire					
BR15I	15 125	Ivory	5-15R	•	•
BR15W	15 125	White	5-15R	•	•
BR15	15 125	Brown	5-15R	•	•
BR15GRY	15 125	Gray	5-15R	•	•
BR15LA	15 125	Light Almond	5-15R	•	•
BR20I	20 125	Ivory	5-20R	•	•
BR20W	20 125	White	5-20R	•	•
BR20	20 125	Brown	5-20R	•	•
BR20GRY	20 125	Gray	5-20R	•	•
BR20BK	20 125	Black	5-20R	•	•
BR20LA	20 125	Light Almond	5-20R	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R

For Configurable Solutions, see Page U-1.

Straight Blade Receptacles Commercial Specification Grade Receptacles


15 & 20A, 125V

Pass & Seymour



Features

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- CR Series: #14 – #10 AWG solid side wire only. BR Series: side and internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.



CR15I

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 C22.2 No. 42
Duplex Receptacles Side Wire					
CR15I	15 125	Ivory	5-15R	•	•
CR15W	15 125	White	5-15R	•	•
CR15	15 125	Brown	5-15R	•	•
CR15GRY	15 125	Gray	5-15R	•	•
CR15LA	15 125	Light Almond	5-15R	•	•
CR20I	20 125	Ivory	5-20R	•	•
CR20W	20 125	White	5-20R	•	•
CR20	20 125	Brown	5-20R	•	•
CR20GRY	20 125	Gray	5-20R	•	•
CR20BK	20 125	Black	5-20R	•	•
CR20RED	20 125	Red	5-20R	•	•
CR20LA	20 125	Light Almond	5-20R	•	•
Duplex Receptacles Back & Side Wire					
BR15I	15 125	Ivory	5-15R	•	•
BR15W	15 125	White	5-15R	•	•
BR15	15 125	Brown	5-15R	•	•
BR15GRY	15 125	Gray	5-15R	•	•
BR15LA	15 125	Light Almond	5-15R	•	•
BR20I	20 125	Ivory	5-20R	•	•
BR20W	20 125	White	5-20R	•	•
BR20	20 125	Brown	5-20R	•	•
BR20GRY	20 125	Gray	5-20R	•	•
BR20BK	20 125	Black	5-20R	•	•
BR20LA	20 125	Light Almond	5-20R	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R

For Configurable Solutions, see Page U-1.