



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AE80BF 80 CFM 1.5 Sones Fan FP Es

Broan/Nutone LLC

Catalog Number	AE80BF
Manufacturer	Broan/Nutone LLC
Description	Ventilation Fan, Rugged 26 Gauge Galvanized Steel, Ceiling Mount, 120 V Ac @ 60 HZ, 26.9 W, 0.3 A, 80 CFM Air Flow, 60 HZ, Round Duct Shape, 4 In Duct Size, White Polymeric, Polymeric Grill Material, Rectangular Grill Shape, 11-3/8 In (L) X 12 In (W) Grill Size, Rugged 26 Gauge Galvanized Steel Housing Material, Rectangular Housing Shape, Permanently Lubricated Plug-In Motor, 9-1/4 In Overall Length, 10 In Overall Width, 5-3/4 In Overall Height, 4 In Duct Diameter, Exhaust, 1.41 LB
Weight per unit	22.5 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	80 CFM
Sound Level	1.5 SONES
Ventilation Area	75 Square Foot

Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height
------	---

Descriptions

Additional Information	Power Rating 26.9 Watt; Includes Permanently Lubricated Plug-In Motor, Tapered Sleeve, Non-Metallic Damper; Excludes Metallic Clatter; Standard Package 4 per Master Carton
Commodity Description	Exhaust Fans
Description	80 CFM 1.5 SONES FAN FP ES

Manufacturer Information

GTIN	00026715236091
Model	Model AE80B
UPC	026715236091

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	CEILING

Packaging

Carton	1
Package	4
Weight Per each	22.5

Uses, Certifications, and Standards

Approval	UL (Canada and US), HVI
----------	-------------------------