



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

BR4242L400F Singleph Mlo LC 400A 42 CKT Flush

Eaton Corp

Catalog Number	BR4242L400F
Manufacturer	Eaton Corp
Description	Eaton BR Main Lug Loadcenter, With Flush or Nema Type 3R Cover, Indoor, 400 A, 22, Aluminum, Flush, Nema 1, 42 Circuits, 42 Spaces, Four-Wire, Three-Phase, Type BR 1-Inch Breakers, 208Y/120, 240V, (1) 250–750 Kcmil or (2) #3/0–250 Kcmil
Weight per unit	54.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	400 A
Cover Type	Cover included
dimensions	6.3100 IN X 16.2200 IN X 54.0000 IN
interrupt rating	25 kAIC
number of spaces	42
Phase	Single-phase

Descriptions

Description	SINGLEPH MLO LC 400A 42 CKT FLUSH
extra long description	ETN BR4242L400F SINGLE PHASE MLO LC
Features	Eaton's BR 1-inch main lug load center is used when a sub-panel is needed to add circuits to an existing service. BR load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits.
Long Description	Eaton BR main lug loadcenter, With flush or NEMA type 3R cover, Indoor, 400 A, 22, Aluminum, Flush, NEMA 1, 42 Circuits, 42 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208Y/120, 240V, (1) 250–750 kcmil or (2) #3/0–250 kcmil
Product Type	Single Phase Mlo LC, 400A, 42 CKT, Flush

Manufacturer Information

Brand	Eaton
GTIN	00786685895444
Manufacturers Part Number	BR4242L400F
UPC	786685895444

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main lug loadcenter

Packaging

Carton	1
Weight Per each	54



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	FLUSH
standard	UL 67,UL 50