

# **B-Twist**<sup>™</sup> WIRE CONNECTOR

MODEL BT2

#### FEATURES/BENEFITS:



- CONNECTION COMES TO TORQUE QUICKLY TO GET THE JOB DONE EFFECIENTLY
- ROUNDED DIAL-TOP PROVIDES FAST, FINGERTIP START
- LONG, SWEPT WINGS OFFER HIGH TORQUE IN A LOW-PROFILE DESIGN
- WIDE, EXPANDING SPRING MAKES FOR EASY STARTS ON EVEN THE LARGEST COMBINATIONS
- WIDE RANGE COVERS FROM 2 #18 TO 2 #8

# **ELECTRICAL**:

VOLTAGE:

GENERAL: 600 V MAX SIGN/LUMINAIRES: 1000 V MAX

PHYSICAL: STANDARDS & SPECIFICATIONS:

HOUSING: GRAY THERMOPLASTIC POLYESTER

INSERT: STEEL PLATING: ZINC

TEMPERATURE: 105° C (221° F)

UL 486 C

UL 94V-2 FLAME RATING CSA- C22.2 NO. 188 ROHS COMPLIANT

IEC 998-2-4



WIRE RANGE & COMBINATIONS:

- Solid and/or stranded wire combinations unless stated otherwise

- Consult website for other combinations not listed


BT2 (RED)


STRIP LENGTH: 1/2"

4 to 6 #22 3 to 6 #20 2 to 6 #18 1 to 6 #16 1 to 6 #14 1 to 5 #12 1 to 4 #10 10 w/ 2 #12 w/ 1 #14

2 #10 w/ 2 #12 w/ 1 #14 3 #12 w/ 2 #14 w/ 1 #16 5 #20 w/ 1 #22

## **DIMENSIONS:**





SALES CONTACT:

## **ORDERING INFO:**

MODEL	COLOR	QUANTITY	CAT. NO.	WEIGHT (lbs)
		BOX OF 100	BT2-1	0.69
BT2	RED	JAR OF 500	BT2-500JR	3.75
		BARREL OF 25.000	BT2-SK	167.50

FACTORY CONTACT:

IDEAL INDUSTRIES, INC.

1375 PARK AVENUE, SYCAMORE, IL, 60178

P: (800) 324-9571 F: (888) 222-6140

E: oem@idealindustries.com