

Specifications



Eaton AH1221L

Eaton locking switch, #14-10 AWG, 20A, 120/277V, Back and side wiring, Key actuator, Maintained closure, Brown, Single-pole, Urea

General specifications

PRODUCT NAME	Eaton locking switch
CATALOG NUMBER	AH1221L
UPC	032664706318
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	1.05 in
PRODUCT WEIGHT	0.22 lb
COMPLIANCES	NAFTA
CERTIFICATIONS	UL Recognized cULus Listed
PRODUCT TYPE	Locking switch



Powering Business Worldwide

Product specifications

ALLOWABLE WIRE SIZE #14-10 AWG

TORQUE RATING 14 lbf-inch

SPECIAL FEATURES Locking

TYPE Switch

AMPERAGE RATING 20A

VOLTAGE RATING 120/277 V

APPLICATION Industrial

WIRING METHOD Back and side

SWITCH TYPE Single-pole

CLOSURE TYPE Maintained

MATERIAL Urea

ACTUATOR Key

COLOR Brown

Resources

MULTIMEDIA [Arrow Hart - Connecting Safety to Reliability since 1890](#)

[Eaton Specification Sheet - AH1221L](#)

SPECIFICATIONS AND DATASHEETS [Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

