BZ Basic Precision Switches (Con't.)

Fig. 1




Fig. 2




Fig. 3




Fig. 4




Fig. 5





Fig. 6



Actuator Style	Ratings	O.F. (Oz)	R.F. (Oz)	P.T. Max (in)	O.T. Min. (in)	D.T. (in)	O.P. (in)	Part Number*	Fig. No.
Flexible Roller Leaf	15 Amps[1]	5	0.5	----	.060	.050	1.125±.030	**BZ-2RL2-A2**	1
One-Way Roller Lever	15 Amps[1]	6	1.5	----	.094	.003 - .020	1.625±.015	**BZ-2RW826-A2**	5
One-Way Roller Lever	15 Amps[1]	8	1.5	----	.060	.015	1.14±.015	**BZ-2RW825-A2**	5
Roller Lever	15 Amps[1]	3.5	0.75	----	.156	.004 - .040	1.188±.030	**BZ-2RW82-A2**	6
Short Roller Lever	15 Amps[1]	6	1.5	----	.094	.003 - .020	1.188±.015	**BZ-2RW822-A2**	4
Short Roller Lever	15 Amps[1]	6	1.5	----	.094	.003 - .020	1.188±.015	**BZ-2RW822**	4
Short Roller Lever	15 Amps[1]	6	1.5	----	.094	.003 - .020	1.188±.015	**BZ-2RW82255-A2-S**	4
Spring Wire Lever	15 Amps[1]	----	----	----	----	----	----	**BZ-2RQ232-A2**	3
Straight Lever	15 Amps[1]	1	----	----	.578	.018 - .145	.750±.060	**BZ-2RW863-A2**	2
Straight Lever	15 Amps[1]	1	0.125	.328	.216	.007 - .050	.750±.030	**BZ-2RW84-A2**	2
Straight Lever	15 Amps[1]	2.5	0.5	----	.219	.007 - .050	.750±.030	**BZ-2RW80-A2**	2
Straight Lever (Adjustable)	15 Amps[1]	2.5	0.5	----	.125	.007 - .050	.670±.880	**BZ-2RW899-A2**	2

CHARACTERISTICS:
O.F. - Operating Force; **R.F.** - Release Force; **P.T.** - Pretravel; **O.T.** - Overtravel; **D.T.** - Differential Travel; **O.P.** - Operating Position.
1 SPDT; 15A-125, 250 or 480 VAC; 1/8 Hp-125 VAC; 1/4 Hp-250 VAC; 1/2 A-125 VDC; UL Code
* **TERMINATION:**
A2 Bottom facing 6-32 NC x .218" screw with cup washers.

Mounting Hole Dimension:

