# Arrow Hart color coded industrial grade L15-30 locking devices

Project Name:	Prepared By:		
Project Number:	Date:		
Catalog Number:	Type:		



Photography is for reference only.

# **Description**

30A, 3Ø 250V/AC, 3-Pole, 4-Wire NEMA L15-30

Blue indicates 250 V/AC





#### Design features for plug & connector

- · All nylon construction
- EPDM gasket seals cord hole from dust and debris
- · Back wire terminal clamps for easy secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires
- Clear cover over wiring compartments allows easy inspection of wiring terminations
- · Rating printed on side of device
- Double dovetail cord clamps with reversible inserts provide secure cord retention over a full range of cord diameters

#### Design features for receptacles

- · Rugged glass filled nylon body
- Clearly marked rating, NEMA configuration and approval listings on receptacle face
- One piece brass contacts offer superior performance and minimum heat rise
- · Back and side wiring terminal clamps for easy, secure wiring

## Design features for flanged inlet & outlet

- All nylon construction
- Mounting holes interchangeable with competitive units
- · Back wire terminal clamps for easy, secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires

Table 1. NEMA L15-30 Color Coded Industrial Grade Locking Devices

Catalog No.	Description	Amps	Volts	Color
☐ AHCL1530P	Color Code ultra grip plug, 3-phase	30	250	Blue & Black
☐ AHCL1530C	Color Coded ultra grip connector, 3-phase	30	250	Blue & Black
☐ AHCL1530R	Color Coded single receptacle, 3-phase	30	250	Blue & Black
☐ AHCL1530F0	Color Coded flanged outlet, 3-phase	30	250	Blue & Black
☐ AHCL1530FI	Color Coded flanged inlet, 3-phase	30	250	Blue & Black

Compliances, specifications and availability are subject to change without notice.



Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

# **Applications**

The new Eaton Arrow Hart color coded locking devices are designed specifically to improve safety and increase labor savings on the job site. Eaton's color coded locking devices are an industry-first solution that uses the six voltage rating color codes consistent with IEC 60309 standards for plugs, connectors, inlets/outlets and receptacles. Color coded locking devices are available in standard NEMA configurations for 20A and 30A applications. Plugs and connectors are built with a durable nylon shell and body to provide long lasting, dependable service in commercial and industrial environments—their ergonomic design has a comfortable feel, and the double dovetail cord clamps with reversible inserts provide secure cord retention over a full range of cord diameters.

Table 2. Specifications


Catalog No.	AHCL1530 Series		
Device Type	Plug & Connector	Single Receptacle	Flanged Inlet & Outlet
NEMA Config	NEMA L15-30	NEMA L15-30	NEMA L15-30
Wiring Type	Back wire	Back & side wire	Back wire
Environmental Specifications	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C (w/o impact) to 60°C (-40°F to 140°F) -25°C (w/impact) to 60°C (-13°F to 140°F)	Flammability: Meets UL94 requirements; V0 rated Temperature Rating: -40°C to 70°C (-40°F to 158°F)	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C (w/o impact) to 60°C (-40°F to 140°F) -25°C (w/impact) to 60°C (-13°F to 140°F)
Electrical Specifications	Dielectric Voltage: Twice the device rating + 1000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)	Dielectric Voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric Voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical Specifications	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device


## Table 3. Materials

Catalog No.	AHCL1530 Series		
Device Type	Plug & Connector	Single Receptacles	Flanged Inlet & Outlet
NEMA Config	NEMA L15-30	NEMA L15-30	NEMA L15-30
Face	N/A	Glass-filled nylon	NEMA L15-30
Base	N/A	Glass-filled nylon	N/A
Mounting Strap	N/A	0.050" thick steel, zinc plated	N/A
Outer Shell	Nylon	N/A	Nylon
Interior Body	Nylon	N/A	Nylon
Terminal Retainer	Polycarbonate	N/A	Polycarbonate
Blades	Brass	N/A	0.062" thick brass (inlet only)
Line Contacts	Bronze, tin plated	0.041" thick brass	0.031" thick bronze (outlet only)
Terminal Clamps/Plates	Steel, tin plated	0.041" thick brass	Steel
Terminal Screws	#10-32 brass, zinc plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)
<b>Ground Screw</b>	#10-32 brass (green)	#10-32 brass (green)	#10-32 brass (green)
Assembly Screws	Steel, nickel plated	N/A	Steel, nickel plated
Gasket/Dust Shield	EPDM	N/A	N/A
Cord Clamp Screws	Steel, nickel plated	N/A	N/A
Cord Clamp	Nylon	N/A	N/A
Ground Contacts	N/A	0.041" thick brass	N/A
Back Plate	N/A	0.041" thick brass, nickel plated	N/A
Mounting Screws	N/A	Steel, zinc plated	Steel, zinc plated

	Project Name:	Prepared By:
Project Number:		Date:
	Catalog Number:	Туре:

### **Product Dimensions**








Figure 1. AHCL1530P

Figure 2. AHCL1530C

Figure 3. Bottom View




Figure 4. AHCL1530R




Figure 5. AHCL1530FO




Figure 6. AHCL1530FI




Figure 7. Top View

# Arrow Hart color coded industrial grade L15-30 locking devices

Project Name:	Prepared By:	
Project Number:	Date:	
Catalog Number:	Type:	

# **Certifications & Compliances**

Catalog No	0.	c (UL) us	<u>(h)</u>	⊕-	F (l) S	NOM 426		<u> </u>
AHCL1530	)P	•				•	•	•
AHCL1530	)C	•				•	•	•
AHCL1530	)R		•	•	•	•	•	•
AHCL1530	)FO	•				•	•	•
AHCL1530FI		•				•	•	•
KEY:	c (UL) us	cULus		(II)	UL	⊕	CSA	

A Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

F®s Fed Spec

NOM NOM

AFTA

ROHS

Compliances, specifications and availability are subject to change without notice.

Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Eaton.com/wiringdevices Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 Canada EatonCanada.ca Eaton.com/wiringdevices

© 2018 Eaton All Rights Reserved Printed in USA Publication No. TD630035EN (rev 1) December 2018 Eaton.mx
Eaton.com/wiringdevices

Electrical Sector

Mexico Operations

Col. Villa Jardin esq.

Carr. Tlalnepantla -Cuautitlan Km 17.8 s/n

Cerrada 8 de Mayo Cuautitlan, Mexico CP 54800



Eaton is a registered trademark.

All other trademarks are property of their respective owners.

