Arrow Hart color coded industrial grade L21-30 locking devices

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Туре:



Photography is for reference only.

Description

30A, 3ØY 120/208V/AC, 4-Pole, 5-Wire NEMA L21-30 = Blue indicates 120/208 V/AC



Design features for plugs & connectors

- All nylon construction
- · EPDM gasket seals cord hole from dust and debris
- · Back wire terminal clamps for easy secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires
- Clear cover over wiring compartments allows easy inspection of wiring terminations
- Rating printed on side of device
- Double dovetail cord clamps with reversible inserts provide secure cord retention over a full range of cord diameters

Design features for receptacles

- Rugged glass filled nylon body
- Clearly marked rating, NEMA configuration and approval listings on receptacle face
- One piece brass contacts offer superior performance and minimum heat rise
- · Back and side wiring terminal clamps for easy, secure wiring

Design features for flanged inlet & outlet

- All nylon construction
- · Mounting holes interchangeable with competitive units
- · Back wire terminal clamps for easy, secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires

Table 1. NEMA L21-30 Color Coded Industrial Grade Locking Devices Catalog No. Description Amps Volts Color

outurog no.	2 ocomption	7 ampo	10110	00101
□ AHCL2130P	Color Coded ultra grip plug, 3-phase	30	120/208	Blue & Black
AHCL2130C	Color Coded ultra grip connector, 3-phase	30	120/208	Blue & Black
AHCL2130R	Color Coded single receptacle, 3-phase	30	120/208	Blue & Black
AHCL2130FO	Color Coded flanged outlet, 3-phase	30	120/208	Blue & Black
AHCL2130FI	Color Coded flanged inlet, 3-phase	30	120/208	Blue & Black

Table 2. NEMA L21-30 Industrial Grade Flat Locking Devices

Catalog No.	Description	Amps	Volts	Color
AHL2130PF	Ultra grip plug, flat cable, 3-phase	30	120/208	Black
AHL2130CF	Ultra grip connector, flat cable, 3-phase	30	120/208	Black

Compliances, specifications and availability are subject to change without notice.



Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Туре:

Applications


The new Eaton Arrow Hart color coded locking devices are designed specifically to improve safety and increase labor savings on the job site. Eaton's color coded locking devices are an industry-first solution that uses the six voltage rating color codes consistent with IEC 60309 standards for plugs, connectors, inlets/outlets and receptacles. Color coded locking devices are available in standard NEMA configurations for 20A and 30A applications. Plugs and connectors are built with a durable nylon shell and body to provide long lasting, dependable service in commercial and industrial environments—their ergonomic design has a comfortable feel, and the double dovetail cord clamps with reversible inserts provide secure cord retention over a full range of cord diameters.

Table 3. Specifications


lubic of opcontoutions			
Catalog No.	AHCL2130 Series		
Device Type	Plugs & Connectors	Single Receptacles	Flanged Inlet & Outlet
NEMA Config	NEMA L21-30	NEMA L21-30	NEMA L21-30
Wiring Type	Back wire	Back & side wire	Back wire
Environmental Specifications	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C (w/o impact) to 60°C (-40°F to 140°F) -25°C (w/impact) to 60°C (-13°F to 140°F) except flat cable: -40°C (w/o impact) to 75°C (-40°F to 167°F)	Flammability: Meets UL94 requirements; V0 rated Temperature Rating: -40°C to 70°C (-40°F to 158°F)	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C (w/o impact) to 60°C (-40°F to 140°F) -25°C (w/impact) to 60°C (-13°F to 140°F)
Electrical Specifications	Dielectric Voltage: Twice the device rating + 1000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)	Dielectric Voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current 5 Temperature Rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric Voltage: ≤300V: 2000V, 301- 600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical Specifications	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device

Table 4. Materials

Catalog No.	AHCL2130 Series		
Device Type	Plug & Connector	Single Receptacles	Flanged Inlet & Outlet
NEMA Config	NEMA L21-30	NEMA L21-30	NEMA L21-30
Face	N/A	Glass-filled nylon	N/A
Base	N/A	Glass-filled nylon	N/A
Mounting Strap	N/A	0.050" thick steel, zinc plated	N/A
Outer Shell	Nylon	N/A	Nylon
Interior Body	Nylon	N/A	Nylon
Terminal Retainer	Polycarbonate	N/A	Polycarbonate
Blades	Brass	N/A	0.062" thick brass (inlet only)
Line Contacts	Bronze, tin plated	0.041" thick brass	0.031" thick bronze (outlet only)
Terminal Clamps/Plates	Steel, tin plated	0.041" thick brass	Steel
Terminal Screws	#10-32 brass, zinc plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)
Ground Screw	#10-32 brass (green)	#10-32 brass (green)	#10-32 brass (green)
Assembly Screws	Steel, nickel plated	N/A	Steel, nickel plated
Gasket/Dust Shield	EPDM	N/A	N/A
Cord Clamp Screws	Steel, nickel plated	N/A	N/A
Cord Clamp	Nylon	N/A	N/A
Ground Contacts	N/A	0.041" thick brass	N/A
Back Plate	N/A	0.041" thick brass, nickel plated	N/A
Mounting Screws	N/A	Steel, zinc plated	Steel, zinc plated



Product Dimensions






Figure 1. AHCL2130P

Figure 2. AHCL2130C






Figure 3. Bottom View







3.06" (77.7mm) 2.03" (51.6mm) (51.6mm) (56.9mm) (55.6mm)




Figure 5. AHCL2130FO

Figure 6. AHCL2130FI

Figure 7. Top View

Arrow Hart color coded industrial grade L21-30 locking devices

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Туре:

Certifications & Compliances

Catalog No.	c (UL) us	ա	<u>ج</u>	F 🕕 S	<u>NOM</u> 426	٩	
AHCL2130P	٠				•	•	•
AHL2130PF					•	•	•
AHCL2130C	•				٠	•	•
AHL2130CF					•	•	•
AHCL2130R		•	•	•	٠	•	•
AHCL2130F0	•				•	•	•
AHCL2130FI	•				•	•	•

@ Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

Compliances, specifications and availability are subject to change without notice.

Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Eaton.com

Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

F AT • N

Powering Business Worldwide

Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 Canada Eaton.Canada.ca Eaton.com/wiringdevices

© 2018 Eaton All Rights Reserved Printed in USA Publication No. TD630040EN (rev 1) December 2018 Electrical Sector Mexico Operations Carr. TilaInepantla -Cuautitlan Km 17.8 s/n Col. Villa Jardin esq. Cerrada 8 de Mayo Cuautitlan, Mexico CP 54800 Mexico Eaton.com/wiringdevices

Eaton is a registered trademark.

All other trademarks are property of their respective owners.