

DESCRIPTION

The Halo LED area and wall light with twist lock photocontrol incorporates sustainable LED technology into a reliable dusk-to-dawn security solution. This fixture provides area coverage equivalent to 100W metal halide or 70W high pressure sodium, while achieving substantial energy and maintenance savings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Construction

- Durable die-cast aluminum housing suitable for wet locations
- UV stable acrylic lens
- Open lens design eliminates collection of debris
- Available in bronze or gray powder coat finish
- Suitable for wall or pole mount
- Fits 1-5/8" EA24 pole mounting arm (available separately)

Electrical

- Maintenance-free LEDs with L70 50,000 hours of life
- Fixture operating temperature range from -30°C to 40°C
- 12,000 cycle NEMA twist lock photocontrol
- Electrical operating voltage 120V 60Hz
- cULus listed for wet locations
- External supply wiring 75°C minimum

Optics

- Patented precision over-optics for maximum efficiency and area light coverage
- 5000K CCT perfect for security applications

Warranty

- 5 year limited warranty




AL3150 LED Area and Wall Light



**Twist Lock Photocontrol
Wall or Pole Mount**

DIMENSIONS

Front View



Side View



ORDERING INFORMATION

Model	Finish
AL3150LPCBZ	Bronze
AL3150LPCGY	Gray

Accessories¹

EA24 = Mounting arm for pole mount
SL3120 = NEMA twist lock photocontrol

Notes: ¹ Order as separate line item.


CERTIFICATION DATA

cULus Wet Location Listed

TECHNICAL DATA

-30°C to 40°C Temperature Rating
External Supply Wiring 75°C Minimum
Wall and Pole Mount

PHOTOMETRICS



Minimum Footcandles (FC)		0.50 FC						0.35 FC	
Mounting Height (Z)		8'		12'		16'		20'	
Catalog Number	Lumens	X	Y	X	Y	X	Y	X	Y
AL3150	3500	23'	46'	30'	60'	32'	64'	40'	80'

X = Forward Throw
Y = Wall Spread
Z = Mounting Heights

Notes:
 Forward throw $X = 1/2 Y$ for wall-mount applications
 See IES files for detailed photometry

TECHNICAL INFORMATION

Series	v(V)	Power (W)	Delivered Lumens	Efficacy (Lum/Watt)	LED Color Temperature (K)	Photocontrol Options
AL3150	120	33.4	3500	104.8	5000K	Twist Lock

DESCRIPTION

The Halo LED area and wall light with twist lock photocontrol incorporates sustainable LED technology into a reliable dusk-to-dawn security solution. This fixture provides area coverage equivalent to 100W metal halide or 70W high pressure sodium, while achieving substantial energy and maintenance savings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Construction

- Durable die-cast aluminum housing suitable for wet locations
- UV stable acrylic lens
- Open lens design eliminates collection of debris
- Available in bronze or gray powder coat finish
- Suitable for wall or pole mount
- Fits 1-5/8" EA24 pole mounting arm (available separately)

Electrical

- Maintenance-free LEDs with L70 50,000 hours of life
- Fixture operating temperature range from -30°C to 40°C
- 12,000 cycle NEMA twist lock photocontrol
- Electrical operating voltage 120V 60Hz
- cULus listed for wet locations
- External supply wiring 75°C minimum

Optics

- Patented precision over-optics for maximum efficiency and area light coverage
- 5000K CCT perfect for security applications

Warranty

- 5 year limited warranty




AL3150 LED Area and Wall Light



**Twist Lock Photocontrol
Wall or Pole Mount**

DIMENSIONS

Front View



Side View



ORDERING INFORMATION

Model	Finish
AL3150LPCBZ	Bronze
AL3150LPCGY	Gray

Accessories¹

EA24 = Mounting arm for pole mount
SL3120 = NEMA twist lock photocontrol

Notes: ¹ Order as separate line item.


CERTIFICATION DATA

cULus Wet Location Listed

TECHNICAL DATA

-30°C to 40°C Temperature Rating
External Supply Wiring 75°C Minimum
Wall and Pole Mount

PHOTOMETRICS



Minimum Footcandles (FC)		0.50 FC						0.35 FC	
Mounting Height (Z)		8'		12'		16'		20'	
Catalog Number	Lumens	X	Y	X	Y	X	Y	X	Y
AL3150	3500	23'	46'	30'	60'	32'	64'	40'	80'

X = Forward Throw
Y = Wall Spread
Z = Mounting Heights

Notes:
 Forward throw $X = 1/2 Y$ for wall-mount applications
 See IES files for detailed photometry

TECHNICAL INFORMATION

Series	v(V)	Power (W)	Delivered Lumens	Efficacy (Lum/Watt)	LED Color Temperature (K)	Photocontrol Options
AL3150	120	33.4	3500	104.8	5000K	Twist Lock