ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0200E2A 200 Va Type Mte Control Transformer

Eaton Corp

Catalog Number	C0200E2A
Manufacturer	Eaton Corp
Description	Eaton Type Mte, Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, SV: 120/115/110V, 55°C, 200 Va , Cu Magnet Wire
Weight per unit	8.0 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	4.1800 IN X 4.5000 IN X 4.2200 IN
kva rating	200 VA
Primary Voltage	230 x 460 V240 x 480 V220 x 440 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	200 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C0200E2A Control transformer, 2
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton type MTE, industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°c, 200 va , cu magnet wire
Product Type	Control Transformer, 200VA, 240/480-120

Manufacturer Information

Brand	Eaton
GTIN	00786680422607
Manufacturers Part Number	C0200E2A
UPC	786680422607

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	8

Uses, Certifications, and Standards

Application	Other
standard	CSA Certified,UL Listed,cUL Certified,RoHS Compliant
Temperature Rating	55 °C