

# Specifications



Photo is representative



## Eaton C0250E5E

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 250 va , cu magnet wire

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0250E5E
<b>UPC</b>	786680420405
<b>PRODUCT LENGTH/DEPTH</b>	5.236 in
<b>PRODUCT HEIGHT</b>	3.819 in
<b>PRODUCT WIDTH</b>	4.488 in
<b>PRODUCT WEIGHT</b>	13.9 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed cUL Certified CSA Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

## Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

## Performance Ratings

<b>PRIMARY VOLTAGE</b>	200/220/440 V, 208/230/460 V, 240/480 V
<b>TEMPERATURE RATING</b>	55°C
<b>VOLT AMPERE RATING</b>	250 VA
<b>SECONDARY VOLTAGE</b>	23/110 V, 24/115 V, 25/120 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0250E5E</a>
-------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com


Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton C0250E5E

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 250 va , cu magnet wire

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0250E5E
<b>UPC</b>	786680420405
<b>PRODUCT LENGTH/DEPTH</b>	5.236 in
<b>PRODUCT HEIGHT</b>	3.819 in
<b>PRODUCT WIDTH</b>	4.488 in
<b>PRODUCT WEIGHT</b>	13.9 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed cUL Certified CSA Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

## Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

## Performance Ratings

<b>PRIMARY VOLTAGE</b>	200/220/440 V, 208/230/460 V, 240/480 V
<b>TEMPERATURE RATING</b>	55°C
<b>VOLT AMPERE RATING</b>	250 VA
<b>SECONDARY VOLTAGE</b>	23/110 V, 24/115 V, 25/120 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0250E5E</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.