



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120
75041-0000, TX Garland
Phone: 214-503-7227
Fax: 214-503-9766



C0300E2AFB 300 Va Mte CTRL XFRMR 240X480V-120V W/Fusing

Eaton Corp

Catalog Number	C0300E2AFB
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, Taps: None, SV: 120/115/110V, 55°C, 300 Va , Cu Magnet Wire
Weight per unit	14.1 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	4.5600 IN X 4.5000 IN X 5.2900 IN
kva rating	300 VA
Primary Voltage	220 X 440 V , 230 X 460 V , 240 X 480 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	300 VA MTE CTRL XFRMR 240X480V-120V W/FUSING
extra long description	ETN C0300E2AFB 300VA Type MTE CPT W
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°c, 300 va , cu magnet wire
Product Type	300VA Type Mte CPT W/ Prim Fuse Block
Special Features	Primary Fuse Block

Manufacturer Information

Brand	Eaton
GTIN	00786680420924
Manufacturers Part Number	C0300E2AFB
UPC	786680420924



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120
75041-0000, TX Garland
Phone: 214-503-7227
Fax: 214-503-9766

Taxonomies, Classifications, and Categories

Category Description CONTROL TRANSFORMERS

Type Industrial Control Transformer

Packaging

Carton 1

Weight Per each 14.1

Uses, Certifications, and Standards

Application Other

standard UL Listed,cUL Certified,CSA Certified,RoHS Compliant

Temperature Rating 55°C