



## ALP2K6 (2)-350 to (6)-2/0 Power Dist Block

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | ALP2K6   |
| Manufacturer     | Nsi Industries   |
| Description      | Power Distribution Block, 2 Primary Openings, 6 Secondary Openings, #6 Awg to 350 MCM Primary Opening Wire Size, #14 to #2/0 Awg Secondary Opening Wire Size, 620 A, 600 V, Clear Acrylic, Maximum Of +90 °C, 5.5 In Overall Length, 2.9 In Overall Width, 3.25 In Overall Height, 1.23 LB |
| Weight per unit  | 1.2 (lbs/each)   |
| Product Category | Power BLKS & Distribution BLKS   |

### Features

|                     |  |
|---------------------|--|
| amperage rating     | 620 Amps Per Pole                              |
| Number of Terminals | 8  |
| Voltage Rating      | 600 V  |
| Warranty            | 1 YEAR   |
| Wire Size           | (2) 350 MCM-6 AWG(Line) - (6) 2/0-14 AWG(Load) |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Black |
|-------|-------|

### Dimensions and Weight

|      |                          |
|------|--------------------------|
| Size | L=5.50 - H=3.25 - W=2.90 |
|------|--------------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | (2)-350 TO (6)-2/0 POWER DIST BLOCK  |
| extra long description | NSI AL-P2-K6 (2) 350 Mcm - 6 Awg Pr  |
| Special Features       | (2) 350 MCM-6 AWG (Line Side) - (6) 2/0-14 AWG (Load Side) - 620 Amps Per Pole |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00662381165695 |
| UPC  | 662381165695   |

### Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | TERMINAL BLOCKS POWER DIST BLOCKS |
| Type                 | Double Primary                    |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 3    |
| Weight Per each | 1.23 |

### Uses, Certifications, and Standards

|             |                  |
|-------------|------------------|
| Application | NSI              |
| Mounting    | 2 Mounting Holes |
| standard    | UL1059           |