

SPECIFICATIONS ASLC50 EXHAUST FAN WITH LIGHT



50 CFM/3.0 Sones @ 0.10" SP.

Grill

White, polymeric grill secured in place via screw mounting through the light housing, dimensions - $11" \times 10^{1}/2"$.

Light Lens

High impact polycarbonate lens, secured in position using integral tabs: easily removed if necessary.

Light Housing

Heavy gauge cold rolled steel c/w baked enamel finish; locks in place on the grill via two integral tabs.

Blower Wheel

One piece polymeric wheel, 41/2" diameter, 1" wide, with 10 fins.

Motor

PSC, plug-in, 4 pole motor, life time lubrication, thermally protected. Rated 120 volts, 60 hz..

Fan Housing

23 ga. Galvanized metal housing, dimensions $7^3\!\%$ " x $7^5\!\%$ " x $5^7\!\%$ "

Duct Collar


Plastic collar for 4" duct connection, comes complete with built in non-metallic back draft damper for quiet operation.

Ventilating Area

For bathrooms up to 45 sq. ft. for other rooms up to 60 sq. ft.

Lighting

26W medium base fluorescent lamp (100W type A19 incandescent bulb can also be used) (lamps not included)



Acceptable for use over tub or shower when installed in a GFCI protected branch circuit.



• Unit Mounting

Rated Type IC for ceilings insulated to R-40. Designed to mount in ceilings with at least 6" of clearance. The unit will mount using the supplied mounting bars with a rough in opening of $7^3/8$ " x $7^5/8$ ". The housing will mount through drywall thickness up to 3/4".

Single Pack Shipping Info

Box Dim: $11\frac{1}{2}$ " x $13\frac{1}{4}$ " x $9\frac{1}{2}$ " Shipping Weight: 6 lbs.

EXPANDED PERFORMANCE											
								Sones	Fan Speed	Maximum	
	Static Pressure (inches of w.g.)							@ .1 SP	RPM	Fan Watts	Amps
	0	0.05	0.1	0.125	0.15	0.2	0.25				
Air Flow - CFM	55	53	50	49	47	44	39	3.0	2125	48	1.4

PROJECT						ARCHITECT			
LOCATION						ENGINEER			
CONTRACTOR						SUBMITTED BY DATE			
FAN MOE NUMBER NUM		IN W.G.	RPM	WATTS	AMPS	SONES	QTY	OPTIONAL EQUIPMENT & REMARKS	



U.S.: 820 Lincoln Avenue
West Chester, Pennsylvania 19380-4466
Tel: (610) 692-7400 • 877-304-3785
Fax: (610) 696-8048

Brampton, Ontario Tel: 800-250-8767 Fax: (905) 456-1015

Canada:

Specifications subject to change without notice. Updated 8-17