

FEATURES & SPECIFICATIONS

INTENDED USE — Inspired by classic fluorescent strip channels, this LED fixture offers a traditional appearance that incorporates the latest technology. Available in several color temperatures, lumen packages and lengths. Ideal for use in commercial, retail, office, warehouse and display applications. Certain airborne contaminants can diminish integrity of acrylic and/or polycarbonate. Click here for Acrylic-Polycarbonate Compatibility table for suitable uses.

CONSTRUCTION — Compact-design channel and cover are formed from code-gauge cold-rolled steel. Easy to install row aligner bracket included for continuous row mounting.

Finish: High-gloss, baked white enamel (standard).

OPTICS — LEDs provide 80+ color rendering index (CRI) at 3500 K, 4000 K and 5000 K. Diffuse polycarbonate lens provides smooth, linear illumination which is designed to resemble the classic look of traditional fluorescent lamps.

Lumen output exceeds 1,000 lumens per foot. Luminaire should be installed in applications where ambient temperatures do not exceed maximum ambient operating temperature of 95 $^{\circ}$ F (35 $^{\circ}$ C).

ELECTRICAL — This fixture is tested to withstand a maximum line surge of 2.5kV/.2kA ring wave for indoor locations. Also tested to withstand a maximum line surge of 2kV/1kA combination wave for indoor locations. For applications requiring higher level of protection additional surge protection must be provided.

INSTALLATION — Fixture may be surface or suspension mounted with appropriate mounting options (see accessories). Aligner locks in place for easy continuous row mounting.

LISTINGS — CSA certified to US and Canadian safety standards and listed suitable for damp locations. Minimum starting temperature at -40°F (-40°C). Maximum ambient operating temperature of 95°F (35°C).

DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at www.designlights.org/QPL to confirm which versions are qualified.

WARRANTY — 5-year limited warranty. Complete warranty terms located at: <u>www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx</u>

Note: Actual performance may differ as a result of end-user environment and application.

All values are design or typical values, measured under laboratory conditions at 25 °C.

 $Specifications \, subject \, to \, change \, without \, notice.$

Catalog Number			
Notes			
Туре			

LED Striplight









ORDERING INFORMATION	Lead times will vary depending on options selected. Consult with your sales representative.	Example: CDS L48 MVOLT DM 40K 80CRI WH

Series	Length	Voltage	Driver	Color temperature	Color rendering index	Options	Finish
CDS LED striplight	L24 24" L48 48" L96 96"	MVOLT 120-277V 347 347V	DM 0-10V dimming	35K 3500 K 40K 4000 K 50K 5000 K	80CRI 80 CRI 90CRI 90 CRI	(blank) None PLR1LVG Plug-in wiring low voltage	WH White

Accessories: Order as separate catalog number.

HC36 Chain hanger and jack chain, 36" (pair)

ZACVH Aircraft cable 10' (one pair)

SQ Swivel-stem hanger (specify length in 2" increments)

rPP20D nLight® air dimming/switching module

** Capable Luminaire

This item is an A+ capable luminaire, which has been designed and tested to provide consistent color appearance and out-of-the-box control compatibility with simple commissioning.

- All configurations of this luminaire meet the Acuity Brands' specification for chromatic consistency
- This luminaire is part of an A+ Certified solution for nLight® or XPoint™ Wireless control networks marked by a shaded background*

To learn more about A+, visit www.acuitybrands.com/aplus.

*See ordering tree for details

INDUSTRIAL

OPERATIONAL DATA

CDS L24 MVOLT (80CRI)				
	Lumens	Wattage	LPW	
35K	2,119		100	
40K	2,177	21	104	
50K	2,274		108	

		CDS L48 MVOLT (80CRI)			
Lumens	Wattage	LPW			
4,146		109			
4,211	38	111			
4,366		115			
	4,146 4,211	4,146 4,211 38			

WEIGHT: (may vary with options or accessories)


L24: 2.6 lbs (1.189 kgs) L48: 5 lbs (2.267 kgs) L96: 10 lbs (4.535 kgs)


CDS L96 MVOLT (80CRI)				
	Lumens	Wattage	LPW	
35K	8,872		115	
40K	9,010	77	117	
50K	9,342		121	

DIMENSIONS

All dimensions are shown in inches (centimeters) unless otherwise noted.

2FT Assembly






INDUSTRIAL:

DIMENSIONS

All dimensions are shown in inches (centimeters) unless otherwise noted.



PHOTOMETRICS

Please see $\underline{www.lithonia.com}.$

