

# Eaton B1520S

Catalog Number: B1520S

Eaton B-Line series strut mounting bracket, Conduit and cable, 1" Height, 1" Length, 1" Width, 0.146lbs, Conduit size EMT: 1.25", Rigid: 1", Conduit strut clamps, 1.125" Min, 1.315" Max cable diameter, 300 lbs load capacity, Pre-galvanized

## General specifications



Product Name	Catalog Number
Eaton B-Line series conduit strut clamp	B1520S
UPC	Product Length/Depth
781011631772	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Certifications
0.146 lb	UL/CUL listed

## Model

### Product Category

Conduit and cable

### Type

Conduit strut clamps

## Specifications

### Size

Conduit size EMT: 1.25 inch, rigid: 1 inch

### Load capacity

300 lbs

### Cable diameter - min

1.125 in

### Cable diameter - max

1.315 in

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - B1520S](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)