



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive  
79936-0000, TX El Paso  
Phone: 915-995-8443  
Fax: 915-245-2106



## CGB5911 1-1/2" Dia Male Cord Grip (1.188-1.375)

Crouse-Hinds

Catalog Number	CGB5911
Manufacturer	Crouse-Hinds
Description	Cord Gland, Steel With Zinc Electroplate and Chromate Finish Coat (Body, Gland Nut); Neoprene (Bushing) Material, CGB Model, 1.188 to 1.375 In Cable/Cord Size, 3.126 In Length, 2.25 In Diameter, Straight Male Connection, 1-1/2 In Thread Size, -25 °C Operating Temperature, +40 °C Operating Temperature, 1.16 LB
Weight per unit	1.2 (lbs/each)
Product Category	Cable & Cord Grips

### Features

connection	Male NPT
dimensions	3.2700 IN X 2.2500 IN X 2.2500 IN

### Material, Color, and Finish

Finish	Zinc Electroplated With Chromate Coated
--------	---

### Dimensions and Weight

Size	1-1/2 in
------	----------

### Descriptions

Description	1-1/2" DIA MALE CORD GRIP (1.188-1.375)
extra long description	CRS-H CGB5911 1 1/2 NPT MALE CORD/C
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round

### Manufacturer Information

Brand	Eaton
GTIN	00782274139203
UPC	782274139203

### Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive  
79936-0000, TX El Paso  
Phone: 915-995-8443  
Fax: 915-245-2106

## Packaging

Carton	1
Package	5
Weight Per each	1.16

## Uses, Certifications, and Standards

Enclosure	Class I Div 2
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 40 Deg C