BatteryCenter


BC-1250F1 & F2

Your Replacement Battery Source

Rechargeable Sealed Lead Acid Battery

(12V 5.0Ah/20hr)





These rechargeable batteries are lead-lead dioxide systems. The dilute sulfuric acid electrolyte is absorbed by separators and thus immobilized. Should the battery be accidentally overcharged producing hydrogen and oxygen, special one-way valves allow the gases to escape thus avoiding excessive pressure build-up. Otherwise, the battery is completely sealed and is, therefore, maintenance-free, leak proof and usable in any position.

Battery Construction									
Component	Positive plate	Negative plate	Container	Cover	Safety valve	Terminal	Separator	Electrolyte	
Raw material	Lead dioxide	Lead	ABS	ABS	Rubber	Copper	Fiberglass	Sulfuric acid	

SPECIFICATION

Nominal voltage	12V
Number of cells	6
Length (mm/inch)	90/3.54
Width (mm/inch)	70/2.76
Height(mm/inch)	101/3.98
Total Height (mm/inch)	107/4.21
Approx.Weight (kg/lbs)	1.62/3.57

General Features

- Absorbent Glass Mat(AGM) technology for efficient gas recombination of up to 99% and freedom from electrolyte maintenance or water adding.
- Not restricted for air transportcomplies with IATA/ICAO Special Provision A67.
- UL-recognized component.
- Can be mounted in any orientation.
- Computer designed lead, calcium tin alloy grid for high power density.
- Long service life, float or cyclic applications.
- Maintenance-free operation.
- Low self discharge.

		1				
Performance Cha	aracteristics					
	20 hour rate (0.25A, 10.5V)	5.0Ah				
Capacity 77°F(25°C)	10 hour rate (0.47A, 10.5V)	4.7Ah				
	5 hour rate (0.86A, 10.5V)	4.3Ah				
	1 hour rate (3.2A, 9.6V)	3.2Ah				
Internal Resistance	Full charged Battery77°F(25°	C):25mΩ				
	104°F(40°C)	102%				
Capacity affected by	77°F(25°C)	100%				
Temperature (20 hour rate)	32°F(10°C)	85%				
	5°F(-15°C)	65%				
Calf Diashanna	Capacity after 3 month storage	90%				
Self-Discharge 68°F(20°C)	Capacity after 6 month storage	80%				
00 T (20 C)	Capacity after 12month storage	60%				
Max. discharge current	77°F(25°C): 75A(5S)					
Charge	Float: 13.6~13.8 V/77°F/(25°C)					
(Constant Voltage)	Cycle: 14.5-14.9 V/77°F/(25°C) Max. Current: 1.25A					

Disc	Discharge Constant Current (Amperes at 77°F 25°C)									
End Points Volts/Cell	5 min	10 min	15 min	30 min	1h	3h	5h	10h	20h	
1.60V	16.8	13.5	10.0	5.22	3.20	1.43	0.91	0.50	0.27	
1.65V	15.9	12.9	9.55	5.01	3.08	1.40	0.90	0.49	0.26	
1.70V	15.0	12.2	9.10	4.79	2.96	1.35	0.88	0.48	0.25	
1.75V	14.0	11.5	8.60	4.56	2.83	1.30	0.86	0.47	0.25	
1.80V	13.0	10.8	8.10	4.31	2.70	1.24	0.82	0.45	0.24	


Discharge Constant Power (Watts at 77°F 25°C)									
End Points Volts/Cell	5 min	10 min	15 min	30 min	45 min	1h	2h	3h	5h
1.60V	33.3	23.2	18.2	10.4	7.74	6.40	3.65	2.63	1.77
1.65V	31.3	21.9	17.2	9.90	7.38	6.13	3.54	2.57	1.73
1.70V	29.2	20.5	16.2	9.36	7.01	5.85	3.42	2.50	1.70
1.75V	27.2	19.2	15.2	8.82	6.63	5.56	3.29	2.42	1.66
1.80V	25.2	17.8	14.2	8.27	6.25	5.26	3.15	2.34	1.62

www.batterycenter.com Toll Free: 800-225-5577




BC-1250F1 & F2 (12V 5.0Ah/20hr)

Charge characteristic curve




CHARGING TIME (HOURS)

Temperature effects on float life




TEMPERATURE (°C)






AMBIENT TEMPERATURE (°C)

Life characteristics of standby use




LIFE (YEAR)

Discharge characteristic (25°C)




DISCHARGE TIME

Cycle service life in relation to depth of discharge




NUMBER OF CYCLES (CYCLES)

Self-discharge characteristic



STORAGE TIME: MONTHS

Temperature effects on capacity



TEMPERATURE (°C)

www.batterycenter.com Toll Free: 800-225-5577