# Eaton BQC220220

## Catalog Number: BQC220220

Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Two-Pole 20 A,10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/AI,BQC,Type BR Loadcenters

### General specifications

**Product Name** 

Eaton BR thermal magnetic circuit

breaker

Catalog Number

BQC220220

**UPC** 

786676371841

Product Length/Depth

3 in

**Product Height** 

2.4 in

**Product Width** 

**Product Weight** 

0.75 lb

Compliances

Certifications

Federal Specifications Classification W-UL 489

C375

**Catalog Notes** 

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single

poles are switch duty rated.



Photo is representative



#### defaultTaxonomyAttributeLabel

Type

Type BQC 1-Inch CTL plug-on circuit breaker

Special features

Includes rejection tab feature

**Amperage Rating** 

(2) Two-Pole 20A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BQ

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BQC

Wire size

#14-4 AWG Cu/AI

Number of poles

Four-pole

#### Resources

**Brochures** 

Loadcenters and Circuit Breakers

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - BQC220220



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.







