



CGB598 1-1/2" Dia Male Cord Grip (.875-1.000) *Crouse-Hinds*

Catalog Number	CGB598
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CGB Cable Gland, Cable Range Min/Max: 0.875-1.000", Non-Armoured and Tray Cable, Non-Armoured, Steel, General Purpose, 1-1/2" NPT
Weight per unit	1.2 (lbs/each)
Product Category	Cable & Cord Grips

Features

connection	Male NPT
dimensions	3.2700 IN X 2.2500 IN X 2.2500 IN
Material	Feraloy Iron Alloy Body and Gland Nut, Neoprene Seal

Material, Color, and Finish

Finish	Zinc Electroplated With Chromate Coated
--------	---

Dimensions and Weight

Size	1-1/2 in
------	----------

Descriptions

Description	1-1/2" DIA MALE CORD GRIP (.875-1.000)
extra long description	CRS-H CGB598 1 1/2 NPT MALE CORD/CA
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round
Long Description	Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 0.875-1.000", Non-armoured and tray cable, Non-armoured, Steel, General purpose, 1-1/2" NPT
Product Type	1 1/2 NPT Male Cord/Cab FTG Neo Bush
Special Features	Non-Armored Gland, Cord Size 0.875 To 1.000 In



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1800 S. May Ave.
73108-0000, OK Oklahoma City
Phone: 405-896-3723
Fax: 405-272-3057

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274135502
Manufacturers Part Number	CGB598
UPC	782274135502

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	1
Package	5
Weight Per each	1.21

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 2
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 40 Deg C