

# Eaton BR2024L125

Catalog Number: BR2024L125

Eaton Eaton BR main lug loadcenter ,No feed-thru lugs,Main lug,125 A,C4,Aluminum,Cover included,Riser panel,Metallic,10 kAIC,BR,24 Circuits,Twenty-four pole,20 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#6-2/0 AWG Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BR2024L125
<b>UPC</b>	<b>Product Length/Depth</b>
786676446907	3.88 in
<b>Product Height</b>	<b>Product Width</b>
21 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
16 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Has notch for brhdk125 hold-down kit.

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs, includes BREQS125 hold-down screw

### Type

Main lug

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

24

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#6-2/0 AWG Cu/Al

### Box size

C1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR  
NEMA 1, 120/240 VAC, 1 PHASE

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR2024L125

Number of wires

3



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)