



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR4040N200G 40/40CKT 200A 1PH Convertible Loadcenter W/GBK

Eaton Corp

Catalog Number	BR4040N200G
Manufacturer	Eaton Corp
Description	BR Style 1-Inch Loadcenter, 40 Spaces, 40 Circuits, 200 A, 120/240 V Ac, Metallic (Enclosure) Material, Aluminum Bus Material, 3.88 In Overall Length, 14.31 In Overall Width, 34.13 In Overall Height, Combination, 35.9 LB
Weight per unit	35.9 (lbs/each)
Product Category	Single Phase Convertible Load

Features

amperage rating	Photoelectric sensor accessory
class	1.0000 IN X 1.0000 IN X 2.2300 IN
Cord Type	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Cover Type	Cover included
dimensions	3.8800 IN X 14.3100 IN X 34.1300 IN
number of spaces	40
Phase	1

Material, Color, and Finish

Color	Photoelectric sensor accessory
material composition	Not Applicable

Dimensions and Weight

Size	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
------	---

Descriptions

Description	40/40CKT 200A 1PH CONVERTIBLE LOADCENTER W/GBK
-------------	--

Manufacturer Information

GTIN	00782116893942
series	Not Applicable
sub brand	Open Office, Retail
UPC	782116893942

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
----------------------	----------------------

Availability

Manufacturer Status	Inactive
Status	Inactive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	35.9

Uses, Certifications, and Standards

Mounting	Combination
standard	UL 50,UL 67