



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRP20L200G BR Pon Loadcntr 200A Mlo 20 Space W/ Ground Bar *Eaton Corp*

Catalog Number	BRP20L200G
Manufacturer	Eaton Corp
Description	Eaton Eaton Type BR 1-Inch Pon Loadcenter, 200 A, Mlo, 20 Spaces, W/ Ground Bar
Weight per unit	21.7 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	200
Cover Type	Cover included
interrupt rating	10
number of spaces	20
Phase	1
Voltage Rating	120/240V
Wattage	Single-pole

Dimensions and Weight

Depth	23
Height	3.88
Size	X3
Width	14.31

Descriptions

Description	BR PON LOADCNTR 200A MLO 20 SPACE W/ GROUND BAR
extra long description	ETN BRP20L200G BR PON LC,200A, MLO,
Features	Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets.
Long Description	Eaton Eaton Type BR 1-inch PON loadcenter, 200 A, MLO, 20 spaces, w/ ground bar
Product Type	BR Pon LC, 200A, Mlo, 20 Space, W/ Ground

Manufacturer Information

Brand	Eaton
GTIN	00786689053277
Manufacturers Part Number	BRP20L200G
UPC	786689053277



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description.....LOADCENTERS & COVERS

Type.....Main lug loadcenter

Packaging

Carton.....1

Weight Per each.....21.7

Uses, Certifications, and Standards

Application.....Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels
and EOEMs

standard.....UL 50,UL 67