



BT2IM0 8" 40LB BLK Barb CBL Tie

Panduit Corporation

Catalog Number	BT2IM0
Manufacturer	Panduit Corporation
Description	The BT2I-M0 Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless-Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Intermediate Cross Section, 8.0" (203MM) Length. Appropriate For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6 With High Resistance to Ultraviolet Light, Are Black In Color and Come In Packages Of 1000.
Weight per unit	0.0019 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	40

Dimensions and Weight

Length	8
Thickness	0.04

Descriptions

Description	8" 40LB BLK BARB CBL TIE
extra long description	PAN BT2I-M0 Dome-Top® BT2I-M0 Barb
Long Description	The BT2I-M0 Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Intermediate cross section, 8.0" (203mm) length. Appropriate for Indoor/Outdoor use, made of Weather Resistant Nylon 6.6 with high resistance to ultraviolet light, are black in color and come in packages of 1000.
Product Type	Dome-Top® BT2I-M0 Barb Tie, Black, Uv PA6.6, 8" L, 40LB, PK10
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	Panduit®
GTIN	00074983413638
Manufacturers Part Number	BT2I-M0
UPC	074983413638



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2301 East Saint Elmo Rd. Suite 105
78744-0000, TX Austin
Phone: 512-443-5600
Fax: 512-443-5601

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

Packaging

Carton	1000
Package	5000
Weight Per each	0.001926

Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant
----------	---