



## CH2L125RSE2P 1PH/CH LC 125A Mlo 2/4 Cir Cu Bus 3R Service Entra

*Eaton Corp*

Catalog Number	CH2L125RSE2P
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenters, Standard, Main Lug Only, 125A, N/A, Copper, Nema 3R, Metallic, Overhead, CH, 2, Two-Pole, 2, Three-Wire, Single-Phase, 120/240 V, #14-1/0 Awg
Weight per unit	7.2 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

### Features

amperage rating	125
interrupt rating	25
media	Yes
number of spaces	2
Phase	1
Voltage Rating	120/240 V
Wattage	Two-pole

### Dimensions and Weight

Depth	9.5
Height	3.13
Size	N/a
Width	4.5

### Descriptions

Description	1PH/CH LC 125A MLO 2/4 CIR CU BUS 3R SERVICE ENTRA
extra long description	ETN CH2L125RSE2P 1 Ph/CH LC 125A ML
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenters, Standard, Main lug only, 125A, N/a, Copper, NEMA 3R, Metallic, Overhead, CH, 2, Two-pole, 2, Three-wire, Single-phase, 120/240 V, #14-1/0 AWG
Product Type	1 PH/CH LC 125A Mlo 2/4 CKT Se Only
Special Features	Standard



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1207 Energy Drive  
75662-0000, TX Kilgore  
Phone: 903-984-8485  
Fax: 903-984-8193

## Manufacturer Information

Brand	Eaton
GTIN	00786676008471
Manufacturers Part Number	CH2L125RSE2P
UPC	786676008471

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main lug loadcenter

## Packaging

Carton	1
Weight Per each	7.18

## Uses, Certifications, and Standards

Application standard	Ind Facilities & Factories - Facility: Power Distribution and Control UL 67,UL 50
----------------------	--------------------------------------------------------------------------------------