

Specifications

Eaton CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG



Photo is representative



General specifications

PRODUCT NAME	Eaton CH surge loadcenter
CATALOG NUMBER	CHEC24L125E
UPC	782116200146
PRODUCT LENGTH/DEPTH	32 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	7 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL Listed
CATALOG NOTES	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included



Powering Business Worldwide

Product specifications

SPECIAL FEATURES Provision only

TYPE Main lug only

AMPERAGE RATING 125 A

BUS MATERIAL Aluminum

NUMBER OF CIRCUITS 32

NUMBER OF SPACES 32

PHASE Single-phase

WIRE SIZE #6-4/0 AWG

BOX SIZE E

ENCLOSURE NEMA 1

INTERRUPT RATING 25 kAIC

Resources

CATALOGS [Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1](#)

MULTIMEDIA [AFCI Educational Video](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - CHEC24L125E](#)

WARRANTY GUIDES [Eaton type CH circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

