



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0050E2A 50 Va Type Mte Control Transformer *Eaton Corp*

Catalog Number	C0050E2A
Manufacturer	Eaton Corp
Description	Control Transformer, 240 X 480, 230 X 460, 220 X 440 V, 120/115/110 V, 2.992 In Overall Length, 2.992 In Overall Width, 2.559 In Overall Height, 1 Phase, Copper Winding (Coil) Material, 55 °C Temperature Rise Rating, 2.6 LB
Weight per unit	2.7 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	3.6100 IN X 3.0000 IN X 3.2600 IN
kva rating	50 VA
Primary Voltage	240 x 480 V220 x 440 V230 x 460 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	50 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C0050E2A 50 VA Type MTE Control
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.

Manufacturer Information

GTIN	00786680422522
UPC	786680422522

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer

Packaging

Carton	1
Weight Per each	2.7

Uses, Certifications, and Standards

standard	CSA Certified,cUL Certified,UL Listed,RoHS Compliant
Temperature Rating	55°C