

# Specifications



## Eaton CHEC24N125ERNSP

Eaton CH surge loadcenter, Renovation terminal blocks, Convertible type CH surge ready loadcenter, 125 A, 24 Circuits

### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC24N125ERNSP
<b>UPC</b>	782116984190
<b>PRODUCT LENGTH/DEPTH</b>	29.5 in
<b>PRODUCT HEIGHT</b>	4.25 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	20 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8ES or CHSUR8EF separately



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	Renovation terminal blocks
<b>TYPE</b>	Surge loadcenter
<b>AMPERAGE RATING</b>	125 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	32
<b>NUMBER OF SPACES</b>	32
<b>PHASE</b>	Single-phase
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
MULTIMEDIA	<a href="#">AFCI Educational Video</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CHEC24N125ERNSP</a>
WARRANTY GUIDES	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

