


# Eaton CHP16L125X1

Catalog Number: CHP16L125X1

Eaton CH main lug loadcenters,PON,CH,125A,X1,Copper,!,NEMA 1 indoor,Steel,25 kAIC,32,Single-pole,16,Three-wire,Single-phase,120/240 V,#6-2/0 AWG



## General specifications

Product Name

Eaton CH main lug loadcenter

UPC

786689059705

Product Height

4 in

Product Weight

9.9 lb

Certifications

UL 50

UL 67

Catalog Number

CHP16L125X1

Product Length/Depth

18.75 in

Product Width

14.3 in

Warranty

Limited lifetime

Catalog Notes

Purchase Size X1 cover seperately

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

CH

### Amperage Rating

125 A

### Bus material

Copper

### Number of circuits

32

### Number Of Poles

Single-pole

### Number of spaces

16

### Phase

Single-phase

### Voltage rating

120/240 V

### Wire size

#8-1/0 AWG Cu

### Box size

X1

### Enclosure

NEMA 1

### Enclosure material

Steel

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP16L125X1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.




[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHP16L125X1

Catalog Number: CHP16L125X1

Eaton CH main lug loadcenters,PON,CH,125A,X1,Copper,!,NEMA 1 indoor,Steel,25 kAIC,32,Single-pole,16,Three-wire,Single-phase,120/240 V,#6-2/0 AWG



## General specifications

Product Name

Eaton CH main lug loadcenter

UPC

786689059705

Product Height

4 in

Product Weight

9.9 lb

Certifications

UL 50

UL 67

Catalog Number

CHP16L125X1

Product Length/Depth

18.75 in

Product Width

14.3 in

Warranty

Limited lifetime

Catalog Notes

Purchase Size X1 cover seperately

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

CH

### Amperage Rating

125 A

### Bus material

Copper

### Number of circuits

32

### Number Of Poles

Single-pole

### Number of spaces

16

### Phase

Single-phase

### Voltage rating

120/240 V

### Wire size

#8-1/0 AWG Cu

### Box size

X1

### Enclosure

NEMA 1

### Enclosure material

Steel

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP16L125X1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)