



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0100E2A 100 Va Mte CTRL XFRMR 240X480V-120V

Eaton Corp

Catalog Number	C0100E2A
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, Taps: None, SV: 120/115/110V, 55°C, 100 Va
Weight per unit	4.0 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	3.4900 IN X 3.3800 IN X 3.3600 IN
kva rating	100 VA
Primary Voltage	220 X 440 V, 230 X 460 V, 240 X 480 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	100 VA MTE CTRL XFRMR 240X480V-120V
extra long description	ETN C0100E2A 100 VA Type MTE Contro
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 100 va
Product Type	100 Va Type Mte Control Transformer

Manufacturer Information

Brand	Eaton
GTIN	00786680422560
Manufacturers Part Number	C0100E2A
UPC	786680422560

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 4

Uses, Certifications, and Standards

Application Other

standard UL Listed, CSA Certified, cUL Certified, RoHS Compliant

Temperature Rating 55°C