



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHU2S 50A 250V Unmetered PWR Panel

Eaton Corp

Catalog Number	CHU2S
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Unmetered, 20A, None, None, None, None, Top, Surface, Circuits: 4, Nema 5-20R2(2), None, None, 3, 0, 0, 125V, None, None
Weight per unit	5.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

dimensions	6.8000 IN X 9.5000 IN X 39.9000 IN
Number of Circuits	798

Descriptions

Description	50A 250V UNMETERED PWR PANEL
extra long description	ETN CHU2S POP Nema 10-50R RECP 50Am
Features	Eaton's unmetered pedestal type power outlet panel provides temporary power outlets for construction sites. Durable, long-lasting units come prewired and assembled without meters, with many easy-access features that make for fast, simple installation. Perfect for underground metering and power where a building or sub-structure is not feasible or desirable.
Long Description	Eaton pedestal mount unmetered, Unmetered, 20A, None, None, None, None, None, Top, Surface, Circuits: 4, NEMA 5-20R2(2), None, None, 3, 0, 0, 125V, None, None
Product Type	Pop Nema 10-50R Recp 50AMP No BRK

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116128181
Manufacturers Part Number	CHU2S
sub brand	None IN
UPC	782116128181

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
igcc	4439
Type	UNMETERED
unspsc code	PILOT LIGHT LENS, LENS TYPE; POLYCARBONATE MATERIAL; BLUE COLOR; ILLUMINATED PUSH PULL UNIT USED ON; NEMA 12/13, IP65 ENCLOSURE; MUSHROOM, TRANSLUCENT CAP STYLE/SHAPE; BASE DIAMETER 1.5 INCH; BASE MATERIAL CHROME PLATED DIE CAST ZINC



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
--------	---

Weight Per each	5
-----------------	---

Uses, Certifications, and Standards

Application	Power Distribution
-------------	--------------------

Mounting	Surface mounting
----------	------------------

standard	UL Listed file E163588;UL 231
----------	-------------------------------