ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CPR10 4" Rigid Connector Threadless

Crouse-Hinds

Catalog Number	CPR10
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CPR Compression Connector, Rigid/Imc, Straight, Non-Insulated, Malleable Iron, 4"
Weight per unit	4.8 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	7.2000 IN X 6.1000 IN X 7.0000 IN
Material	Malleable Iron

Dimensions and Weight

Size	4 in

Descriptions

Construction	Concrete Tight
Description	4" RIGID CONNECTOR THREADLESS
extra long description	CRH CPR10 4 RGD CMP CONN
Features	Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea
Long Description	Eaton Crouse-Hinds series CPR compression connector, Rigid/IMC, Straight, Non-insulated, Malleable iron, 4"
Product Type	4 RGD CMP Conn

Manufacturer Information

Brand	Eaton
GTIN	00784564122100
Manufacturers Part Number	CPR10
UPC	784564122100

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression Connector

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.75

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL 514B, CUL