



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0250E1B 250 Va Type Mte Control Transformer *Eaton Corp*

Catalog Number	C0250E1B
Manufacturer	Eaton Corp
Description	Control Transformer, 120 X 240 V, 24 V, 250 Va, 4.37 In Overall Length, 4.488 In Overall Width, 3.819 In Overall Height, 50/60 HZ, 1 Phase, Copper Winding (Coil) Material, 55 °C Temperature Rise Rating, 10.1 LB
Weight per unit	10.4 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	3.8000 IN X 4.5000 IN X 4.2200 IN
kva rating	250 VA
Primary Voltage	120 x 240 V
Secondary Voltage	24 V
Tap Size	NONE

Descriptions

Description	250 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C0250E1B 250 VA Type MTE Contro
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.

Manufacturer Information

GTIN	00786680423024
UPC	786680423024

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer

Packaging

Carton	1
Weight Per each	10.4

Uses, Certifications, and Standards

standard	UL Listed,cUL Certified,CSA Certified,RoHS Compliant
Temperature Rating	55°C