



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CB5 1-1/2" Malleable Clampback

*Crouse-Hinds*

Catalog Number	CB5
Manufacturer	Crouse-Hinds
Description	
Weight per unit	0.1600 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

Material	MALLEABLE IRON
----------	----------------

### Dimensions and Weight

Size	1-1/2 In
------	----------

### Descriptions

Description	1-1/2" MALLEABLE CLAMPBACK
Product Type	1 1/2 Clamp Back

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564205056
UPC	784564205056

### Taxonomies, Classifications, and Categories

Category Description	RIGID STRAPS & CLAMPBACKS
Type	Clamp Back

### Packaging

Carton	25
Weight Per each	0.16

### Uses, Certifications, and Standards

Application	Rigid/IMC Conduit
standard	UL, cUL

# Thin Wall Conduit Fittings (for EMT Conduit)

Pulling Elbows, Straps, Clamps, Clampbacks/Spacers


## 90 DEGREE PULLING ELBOWS – ZINC DIE CAST

### Applications:

- To connect EMT to form a 90° bend, or to connect EMT to box or enclosure
- Removable cover and gasket facilitate wire pulling

### EMT to Box

UL File No. E-19189



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
850EB DC	1/2"	20	17
875EB DC	3/4"	15	24
8100EB DC	1"	6	54
8125EB DC	1 1/4"	3	80

### EMT to EMT

UL File No. E-19189



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
850EE DC	1/2"	20	15
875EE DC	3/4"	15	22
8100EE DC	1"	6	52
8125EE DC	1 1/4"	3	80

## CLAMPBACKS/SPACERS – MALLEABLE IRON

### Applications:

- Provides space between conduit and mounting surface

### Standard Materials:

- Stamped steel – 1/2" to 1 1/2"
- Malleable iron – 2" to 6"

### Standard Finish:

- Zinc plated

UL File No. E-184283



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
CB1*	1/2"	25	8
CB2*	3/4"	25	10
CB3*	1"	25	12
CB4*	1 1/4"	25	21
CB5*	1 1/2"	25	42
CB6	2"	10	40
CB7	2 1/2"	10	49
CB8	3"	10	62
CB9	3 1/2"	10	91
CB10	4"	10	110
CB11†	5"	5	135
CB12†	6"	5	225

\*Stamped steel.  
†Not UL Listed.

## STRAPS – STEEL GALVANIZED Two Hole

UL File No. E-184283



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
497 1	1/2"	250	2
497 2	3/4"	150	3
497 3	1"	100	5
497 4	1 1/4"	50	8
497 5	1 1/2"	50	13
497 6	2"	25	14
496 9	2 1/2"	25	19
496 10	3"	25	23
496 11	3 1/2"	25	93
496 12	4"	10	108

## CLAMPS – MALLEABLE IRON

UL File No. E-184283



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
516*	2 1/2"	5	104
517*	3"	2	120
518*	3 1/2"	2	150
519*	4"	2	220

\*Also for use with rigid/IMC conduit.

## CLAMPS – STEEL

### Applications:

- To support EMT conduit to mounting surface

### Heavy Gauge

UL File No. E-184283



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
200	1/2"	100	5
201	3/4"	100	6
202	1"	100	6
203	1 1/4"	50	13
204	1 1/2"	25	17
205	2"	25	20
206*	2 1/2"	25	64
207*	3"	25	71
208*	3 1/2"	10	120
209*	4"	10	130

\*Not UL Listed.

# Thin Wall Conduit Fittings (for EMT Conduit)

## Nailing Straps – Steel

EMT Fittings

### NAILING STRAPS – CAST STEEL

#### Applications:

- To secure EMT conduit, flexible metallic conduit, armoured cable and metal-clad cable to mounting surface

#### Standard Material:

- Cast steel

#### Standard Finish:


- Zinc plated



Cat. #	Conduit Sizes		Wt. Lbs. Per 100
	EMT	Rigid	
NS 1	1/2"	3/8"	2
NS 2	3/4"	1/2"	2
NS 3	1"	3/4"	3

#### Dimensions (in Inches):

Cat. #	A	B	C	D
NS 1	3/16	1	1 7/8	3/4
NS 2	3/4	1 1/4	2	15/16
NS 3	3/16	1 1/2	2 1/2	1 1/8



### NAILING STRAPS – STAMPED STEEL

#### Applications:

- To secure EMT conduit

#### Certifications and Compliances:

- UL File No. E-184283

#### Standard Material:

- Pre-galvanized stamped steel



Cat. #	Conduit Sizes		Unit Qty.	Wt. Lbs. Per 100
	EMT	Rigid		
NSS1	1/2"	3/8"	100	2
NSS2	3/4"	1/2"	100	2
NSS3	1"	3/4"	100	3

#### Dimensions (in Inches):

Cat. #	A	B	C	Radius
NSS1	2.100	1.040	0.080	0.350
NSS2	2.300	1.275	0.080	0.460
NSS3	2.200	1.500	0.080	0.580

