



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7520 Eastgate Blvd Suite 100  
37122-0000, TN Mt. Juliet  
Phone: 615-257-4146  
Fax: 615-257-4147



## CGB5913 1-1/2" Dia Male Cord Grip (1.375-1.625)

Crouse-Hinds

Catalog Number	CGB5913
Manufacturer	Crouse-Hinds
Description	Cord Gland, Feraloy Iron Alloy With Electrogalvanized and Aluminum Acrylic Paint (Body/Gland Nut);Neoprene (Bushing) Material, CGB Model, 1.375 to 1.625 In Cable/Cord Size, 3.438 In Length, 3 In Diameter, Straight Male Connection, 1-1/2 In Thread Size, -25 °C Operating Temperature, +40 °C Operating Temperature, 2.68 LB
Weight per unit	2.7 (lbs/each)
Product Category	Cable & Cord Grips

### Features

connection	Male NPT
dimensions	3.4400 IN X 3.0000 IN X 3.0000 IN

### Material, Color, and Finish

Finish	Zinc Electroplated With Chromate Coated
--------	---

### Dimensions and Weight

Size	1-1/2 in
------	----------

### Descriptions

Description	1-1/2" DIA MALE CORD GRIP (1.375-1.625)
extra long description	CRS-H CGB5913 1 1/2 NPT MALE CORD/C
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274139401
UPC	782274139401

### Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7520 Eastgate Blvd Suite 100  
37122-0000, TN Mt. Juliet  
Phone: 615-257-4146  
Fax: 615-257-4147

## Packaging

Carton	1
Package	2
Weight Per each	2.68

## Uses, Certifications, and Standards

Enclosure	Class I Div 2
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 40 Deg C