



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSB20AC4I 20A 120/277VAC B+S Wire Comm 4W SW Iv

Pass & Seymour/Legrand

Catalog Number	CSB20AC4I
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 4 Poles, 4 Ways, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Ivory, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.19 LB
Weight per unit	0.1905 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Four pole
actuator	Toggle
amperage rating	20
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Incandescent, Halogen, LED, Xenon, CFL, Universal, Fluorescent
Number of Gangs	1
Number of Switches	1.0
Poles	4-Way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC B+S WIRE COMM 4W SW I
extra long description	P&S CSB20AC4I 20A 120/277VAC B+S WI

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126372
Manufacturers Part Number	CSB20AC4I
UPC	785007126372



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.1905

Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting	WALL
standard	UL, CSA, FEDSPEC, CULUS, UL 498/20, FEDSPEC