



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CH32B150J 32C 150A 1PH MB Loadcenter

Eaton Corp

Catalog Number	CH32B150J
Manufacturer	Eaton Corp
Description	CH Style Load Center, 32 Spaces, 32 Circuits, 150 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Copper Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 34.13 In Overall Height, 22.9 LB
Weight per unit	22.9 (lbs/each)
Product Category	Single Phase Main Breaker Load

### Features

amperage rating	150 WTT
Box Size	J
cover	Ch8jf-combination, ch8js-surface, not included
Cover Type	Ch8jf-combination, ch8js-surface, not included
dimensions	86.6902centimetreX36.3474centimetreX98.5520millimetre
main circuit breaker	CSR
max amps	150
max poles	32
Number of Wires	Three-wire
Phase	1 W

### Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

### Dimensions and Weight

Size	J
------	---

### Descriptions

Description	32C 150A 1PH MB LOADCENTER
extra long description	ETN CH32B150J CH 3/4-inch loadcente

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113098081
UPC	782113098081



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	MAIN BREAKER
unspsc code	39121101

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	22.9

## Uses, Certifications, and Standards

Enclosure	NEMA 1
standard	UL 67;UL 50