

# Cable Tray Ground Clamp

## Type CTGC

### Use:

Terminates ground wire to cable tray.

### Features:

- For aluminum or copper conductors.
- 1/4" hex wrench tightens both tray and conductor set screws.
- Tray-gripping serrations bite through insulating oxide on surface of aluminum tray.
- For 1/2" max. straight tray rail, or 1/4" 90° tray rail.
- Conductor size #6 to 250 MCM

### Material/Finish:

Clamp - Extruded Aluminum/Tin Plated  
Screws - Steel/Zinc Electroplated

### Options:

Stainless steel screws are available - add suffix **SS**

### Third Party Certification:





UL Listed: E-24264



CSA Certified: 009795

For copper conductors only.

Catalog Number	Conductor Range AWG/kcmil		Dimensions in Inches	
	Min.	Max.	A	B
CTGC-6-25A	6	250	2	1 1/4



Type CTGC

### Applicable Third Party Standards:

UL Standard: 467

CSA Standard: C22.2 No. 41

NEC 250-77 and 318-6

# Ground Rod Clamps

## Commodity Grade

## Type GRC

### Use:


To ground a conductor to a driven ground rod.

### Features:

- High strength cast bronze.
- Suitable for direct burial.

### Material:

Cast Bronze



Type GRC

### Third Party Certification:



UL Listed: E-24264

Suitable for direct burial.



CSA Certified: 057250

### Applicable Third Party Standards:

UL Standard 467

CSA Standard: C22.2 No. 41

National Electrical Code

Articles 250-112, 250-113 and 250-115

NEMA: FB-1

Catalog Number	Ground Rod Size Inches	Screw Thread Size (UNC-2A)	Conductor Range AWG		Dimensions in Inches		
			Min.	Max.	Max. Height	Max. Width Across Open End	Side Length
GRC-50-02B	1/2	3/8 - 16	10	2	1 13/16	1 3/16	1 1/8
GRC-62-02B	5/8	3/8 - 16	10	2	1 7/8	1 5/16	5/8
GRC-62-10B	3/4	3/8 - 16	8	1/0	1 15/16	7/8	1
GRC-75-10B	1	3/8 - 16	8	1/0	2 3/16	1 1/16	1 1/8

# Cable Tray Ground Clamp

## Type CTGC

### Use:

Terminates ground wire to cable tray.

### Features:

- For aluminum or copper conductors.
- 1/4" hex wrench tightens both tray and conductor set screws.
- Tray-gripping serrations bite through insulating oxide on surface of aluminum tray.
- For 1/2" max. straight tray rail, or 1/4" 90° tray rail.
- Conductor size #6 to 250 MCM

### Material/Finish:

Clamp - Extruded Aluminum/Tin Plated  
Screws - Steel/Zinc Electroplated

### Options:

Stainless steel screws are available - add suffix **SS**

### Third Party Certification:





UL Listed: E-24264



CSA Certified: 009795

For copper conductors only.

Catalog Number	Conductor Range AWG/kcmil		Dimensions in Inches	
	Min.	Max.	A	B
CTGC-6-25A	6	250	2	1 1/4



Type CTGC

### Applicable Third Party Standards:

UL Standard: 467

CSA Standard: C22.2 No. 41

NEC 250-77 and 318-6

# Ground Rod Clamps

## Commodity Grade

## Type GRC

### Use:


To ground a conductor to a driven ground rod.

### Features:

- High strength cast bronze.
- Suitable for direct burial.

### Material:

Cast Bronze



Type GRC

### Third Party Certification:



UL Listed: E-24264

Suitable for direct burial.



CSA Certified: 057250

### Applicable Third Party Standards:

UL Standard 467

CSA Standard: C22.2 No. 41

National Electrical Code

Articles 250-112, 250-113 and 250-115

NEMA: FB-1

Catalog Number	Ground Rod Size Inches	Screw Thread Size (UNC-2A)	Conductor Range AWG		Dimensions in Inches		
			Min.	Max.	Max. Height	Max. Width Across Open End	Side Length
GRC-50-02B	1/2	3/8 - 16	10	2	1 13/16	1 3/16	1 1/8
GRC-62-02B	5/8	3/8 - 16	10	2	1 7/8	1 5/16	5/8
GRC-62-10B	3/4	3/8 - 16	8	1/0	1 15/16	7/8	1
GRC-75-10B	1	3/8 - 16	8	1/0	2 3/16	1 1/16	1 1/8